

Digital Multimeter



72-7925

Specifications

Basic Functions	Range	Best Accuracy
DC Voltage	200 mV / 2 V / 20 V / 200 V	$\pm (0.5\% + 1)$
	1,000 V	$\pm (0.8\% + 2)$
AC Voltage	2 V / 20 V / 200 V	$\pm (0.8\% + 3)$
	750 V	$\pm (1.2\% + 3)$
DC Current	2 mA	$\pm (0.8\% + 1)$
	200 mA	$\pm (1.5\% + 1)$
	10 A / 20 mA	$\pm (2\% + 5)$
AC Current	2 mA	$\pm (1\% + 3)$
	200 mA	$\pm (1.8\% + 3)$
	10 A / 20 A	$\pm (3\% + 5)$
Resistance	200 Ω	$\pm (0.8\% + 3)$
	2 K Ω	$\pm (0.8\% + 1)$
	20 K Ω	$\pm (0.8\% + 10)$
	2 M Ω	$\pm (0.8\% + 1)$
	20 M Ω	$\pm (1\% + 2)$



Digital Multimeter



Specifications

Basic Functions	Range	Best Accuracy
Capacitance	2 nF / 200 nF / 20 μ F	\pm (4% + 3)
Temperature ($^{\circ}$ F)	-40 $^{\circ}$ F to 32 $^{\circ}$ F	\pm (4% + 4)
	32 $^{\circ}$ F to 752 $^{\circ}$ F	\pm (2% + 8)
	752 $^{\circ}$ F to 1,832 $^{\circ}$ F	\pm (3% + 10)
Frequency	2 KHz	\pm (2% + 5)
	20 KHz	\pm (1.5% + 5)

Special Functions

Diode	Yes
Continuity Buzzer	
Transistor	
Sleep Mode	
Low Battery Display	
Input Impedance for DC Voltage Measurement	Around 10 M Ω
Maximum Display	1,999

General Characteristics

Power	9 V battery (6F22)
LCD Size	63 \times 32 mm
Product Colours	Grey, holster - red
Product Net Weight	Around 310 g (including holster)
Product Size	172 \times 83 \times 38 mm
Standard Accessories	Test lead, battery, English manual, point contact temperature probe, holster
Optional Accessories	Clip-on test lead light, (UT-TL) built-in test lead light, (UT-L1) built-in test lead light plus (UT-L2)
Standard Individual Packing	Gift box
Standard Quantity per Carton	40 pcs
Standard Carton Measurement	594 \times 414 \times 334 mm (0.082CBM per standard carton)
Standard Carton Gross Weight	Around 21.4 kg

Part Number Table

Description	Part Number
Multimeter, Digital	72-7925

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMATM is the registered trademark of the Group. © Premier Farnell plc 2012.