


Super Vu-Tron® III Types SJOOW/SOOW

105°C 300 and 600 Volt UL/CSA Portable Cord



TYPE SJOOW – 300 VOLT – UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M ^(S)	STD. CTN.
				INCHES	mm	INCHES	mm			
02001*	2	18	41/34	0.030	0.76	0.310	8.00	10	56	1000'
02002*	3	18	41/34	0.030	0.76	0.320	8.12	10	65	1000'
02003*	4	18	41/34	0.030	0.76	0.345	8.76	7	80	250'
02004*	2	16	65/34	0.030	0.76	0.315	8.00	13	68	1000'
02005*	3	16	65/34	0.030	0.76	0.335	8.51	13	80	250'
02006*	4	16	65/34	0.030	0.76	0.370	9.40	10	95	250'
02007*	2	14	41/30	0.030	0.76	0.370	9.40	18	90	250'
02008*	3	14	41/30	0.030	0.76	0.375	9.52	18	110	250'
02009*	4	14	41/30	0.030	0.76	0.405	10.29	15	130	250'

TYPE SOOW – 600 VOLT – UL/CSA

CATALOG NUMBER	NO. OF COND.	AWG SIZE	COND. STRAND	NOMINAL INS. THICKNESS		NOMINAL O.D.		CURRENT AMPS†	APPROX. NET WT. LBS/M ^(S)	STD. CTN.
				INCHES	mm	INCHES	mm			
02031*	2	18	41/34	0.030	0.76	0.365	9.27	10	75	250'
02032*	3	18	41/34	0.030	0.76	0.375	9.53	10	80	250'
02033*	4	18	41/34	0.030	0.76	0.400	10.16	7	110	250'
02034*	2	16	65/34	0.030	0.76	0.370	9.40	13	75	250'
02035*	3	16	65/34	0.030	0.76	0.395	10.80	13	100	250'
02036*	4	16	65/34	0.030	0.76	0.425	10.80	10	120	250'
02021*	5	16	65/34	0.030	0.76	0.515	13.08	8	150	250'
02037*	2	14	41/30	0.045	1.14	0.510	12.95	18	155	250'
02038*	3	14	41/30	0.045	1.14	0.525	13.34	18	165	250'
02039*	4	14	41/30	0.045	1.14	0.575	14.61	15	215	250'
02022*	5	14	41/30	0.045	1.14	0.675	17.15	12	285	250'
02041*	2	12	65/30	0.045	1.14	0.590	14.99	25	200	250'
02042*	3	12	65/30	0.045	1.14	0.600	15.24	25	250	250'
02043*	4	12	65/30	0.045	1.14	0.650	16.51	20	280	250'
02023*	5	12	65/30	0.045	1.14	0.730	18.54	16	315	250'
02045*	3	10	104/30	0.045	1.14	0.660	16.76	30	320	250'
02046*	4	10	104/30	0.045	1.14	0.710	18.03	25	375	250'
02024*	5	10	104/30	0.045	1.14	0.770	19.56	20	432	250'

* Non-stock item available by special order; minimum quantity purchase required.

† Green conductor for grounding only. Ampacities based on NEC table 400.5(A).

^(S)Actual shipping weight may vary.

Product Construction:

Conductors:

- 18 through 10 AWG fully annealed stranded bare copper per ASTM B-174

Insulation:

- Premium-grade, color-coded, oil-resistant 105°C EPDM
- Color code: See chart below

Jacket:

- Super Vu-Tron® III, yellow
- Temperature range: -50°C to +105°C UL/CSA
- Voltage rating: 300 volts Type SJOOW, 600 volts Type SOOW

Jacket Marking:

- CAROL SUPER VU-TRON® III (SIZE) (mm²) 105°C (UL) WATER RESISTANT SJOOW (OR SOOW) CSA -50°C FT-1 --- P-123-103 MSHA (VOLTS) RoHS MADE IN USA

Applications:

- Machine tools
- Power tools
- Dockside power applications
- Motor leads
- Portable machinery
- Cranes
- Submersible pumps

Features:

- Excellent flexibility in cold temperatures
- Last longer in flex applications
- Integral Flexfill®
- Ozone-sunlight (UV)- and weather-resistant
- UL Listed and CSA Certified for indoor and outdoor use
- Water-resistant, sunlight (UV)- resistant
- Safety-colored
- High heat and flame resistance
- Resistant to oils, acids and chemicals
- Excellent abrasion and cut resistance

Industry Approvals:

- UL Flexible Cord - UL Subject 62
- CSA Flexible Cord - C22.2-49
- MSHA Approved
- RoHS Compliant

Packaging:

- 250' (76.2 m), 500' (152.4 m), 1000' (304.8 m)
- Other put-ups available on special order

COLOR CODE CHART

NO. OF CONDUCTORS	COLOR
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green
5	Black, White, Red, Orange, Green

