

QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange



QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

PACKAGE DIMENSIONS



NOTE:

Dimensions for all drawings are in inches (mm).

APPLICATIONS

- Backlighting
- Status indication for consumer electronics and other equipment

DESCRIPTION

Designed with a reflective housing, these super bright surface mount LEDs offer uniform lighting and high light output performance.

FEATURES

- Reflector package
- AllInGaP technology for -R, -E, -O, -Y and -AG
- InGaN/SiC technology for -IG and -IB
- Wide viewing angle of 130°
- Water clear optics
- Moisture-proof packaging
- Available in 0.315" (8mm) width tape on 7" (178mm) diameter reel; 2,000 units per reel

SURFACE MOUNT LED LAMP

SUPER BRIGHT REFLECTOR

QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange

QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

ABSOLUTE MAXIMUM RATINGS (T_A =25°C Unless otherwise specified)

Parameter	Symbol	QTLP680C					Units
		-R	-E	-O	-Y	-AG	
Continuous Forward Current	I _F	30	30	30	25	30	mA
Peak Forward Current (f = 1.0 KHz, Duty Factor = 1/10)	I _{FM}	160	160	160	120	160	mA
Reverse Voltage	V _R	5	5	5	5	5	V
Power Dissipation	P _D	72	72	72	60	72	mW
Operating Temperature	T _{OPR}	-40 to +85					°C
Storage Temperature	T _{STG}	-40 to +90					°C
Lead Soldering Time	T _{SOL}	260 for 5 sec					°C

ABSOLUTE MAXIMUM RATINGS (T_A =25°C Unless otherwise specified)

Parameter	Symbol	QTLP680C		Units
		-IB	-IG	
Continuous Forward Current	I _F	30	30	mA
Peak Forward Current (f = 1.0 KHz, Duty Factor = 1/10)	I _{FM}	100	100	mA
Reverse Voltage	V _R	5	5	V
Power Dissipation	P _D	120	120	mW
Operating Temperature	T _{OPR}	-40 to +85		°C
Storage Temperature	T _{STG}	-40 to +90		°C
Lead Soldering Time	T _{SOL}	260 for 5 sec		°C

QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange

QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

Fig. 1 Forward Current vs. Forward Voltage




Fig. 2 Relative Luminous Intensity vs. DC Forward Current




Fig. 3 Relative Intensity vs. Peak Wavelength




Fig. 4 Radiation Diagram





Fig. 5 Maximum Forward Current vs. Ambient Temperature



QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange

QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

TYPICAL PERFORMANCE CURVES (QTLP680C-R, -E, -O, -Y and -AG)

Fig. 1 Forward Current vs. Forward Voltage




Fig. 2 Relative Luminous Intensity vs. DC Forward Current




Fig. 3 Relative Intensity vs. Peak Wavelength




Fig.4 Radiation Diagram





Fig.5 Maximum Forward Current vs. Ambient Temperature



QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange

QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

TYPICAL PERFORMANCE CURVES (QTLP680C-IG and IB)

Fig. 1 Forward Current vs. Forward Voltage




Fig. 2 Relative Luminous Intensity vs. DC Forward Current




Fig. 3 Relative Intensity vs. Peak Wavelength




Fig. 4 Radiation Diagram





Fig. 5 Maximum Forward Current vs. Ambient Temperature



QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange


QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green


QTLP680C-IG True Green

QTLP680C-IB Blue

RECOMMENDED PRINTED CIRCUIT BOARD PATTERN



RECOMMENDED IR REFLOW SOLDERING PROFILE



QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange


QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

TAPE AND REEL DIMENSIONS



Dimensional tolerance is ± 0.1 mm unless otherwise specified

Angle: ± 0.5

Unit: mm

QTLP680C-R Red

QTLP680C-E Orange

QTLP680C-O Yellow-Orange

QTLP680C-Y Yellow

QTLP680C-AG Yellow-Green

QTLP680C-IG True Green

QTLP680C-IB Blue

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fairchild Semiconductor:

[QTL P680CAGTR](#) [QTL P680CETR](#) [QTL P680CIBTR](#) [QTL P680CIGTR](#) [QTL P680COTR](#) [QTL P680CRTR](#)
[QTL P680CYTR](#)