





SECTION A-A

MATERIAL : UNPLATED BRASS(C2600T)
HARDNESS : 62+/-7 ROCKWELL 30T SCALE
(VICKERS HARDNESS : HV104-148)

NOTES:


1. MATERIALS: PHOSPHOR BRONZE, 1/2 HARD, 0.3mm THICKNESS
2. FINISHES: POST TIN PLATED
(1.0 μ m MIN. TIN OVER 0.3 μ m MIN. COPPER)
3. PRODUCT SPECIFICATION: PS-49748-001
4. PACKAGING SPECIFICATION: PK-49748-001
5. APPLICABLE MAGNET WIRE RANGE : AWG #25.5 - #19(280 - 1300 CMA)
6. INSULATION WIRE RANGE : TFS-19 ~ 21 TEFLON TUBING
PER THE FOLLING CS-49748-001
7. TEST TAB INSERTION & WITHDRAWAL FORCE
(MEASURED BY PUSH-PULL GAUGE : USED 0.8t UNPLATED TAB)

INSERTION FORCE(Kgf)	WITHDRAWAL FORCE(Kgf)	FINISH
INITIAL	INITIAL	
5.5kgf MAX.	2.5kgf MIN.	TIN PLATED




TRADE MARK
(MK1)

SECTION A-A



SECTION B-B



REVISED EC NO: KOR2014-0002 DRWN:SKCHD CHKD:SHCHU APPR:YSK IM02 B1	DESCRIPTION	QUALITY SYMBOLS ▼=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 7/1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY JB . JIN	DATE 2004/03/16	TITLE .110 REC TERMINAL (MAGNET WIRE)				
			4 PLACES	± ---	± ---	CHECKED BY WY . YANG	DATE 2004/03/16					
			3 PLACES	± ---	± ---							
			2 PLACES	± 0.30	± ---							
			1 PLACE	± 0.30	± ---							
	0 PLACE	± ---	± ---	APPROVED BY CW . LEE	DATE 2004/03/16	molex		DOCUMENT NO. SD-49748-001	SHEET NO. 1 OF 1			
	ANGULAR ± 1 °			MATERIAL NO. 497489001								
	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[49748-9001](#)