





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECO-16-004940	06AUG2016	NK	MZ



RECOMMENDED PC BOARD LAYOUT

- 1 3.81um [.000150] MIN TIN-LEAD OVER 0.76um [.000030] MIN NICKEL.
- 2 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.23 [.206] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 3 3.81um [.000150] MIN TIN OVER 0.76um [.000030] MIN NICKEL.
- 4 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 5.23 [.206] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

OBSOLETE	4	207612-7
	3	207612-6
	2	207612-3
	1	-207612-1
CONTACT FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 08/06/92	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK J.McCLINTON 8-11-92			
		APVD -	NAME		
		PRODUCT SPEC 108-10033	SOCKET HEADER ASSEMBLY, 10 POSN, IN-LINE, METRIMATE		
MATERIAL HOUSING: NYLON, RED		FINISH CONTACTS: SEE TABLE	SIZE A2	CAGE CODE 00779	DRAWING NO C-207612
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV J