


ELFD SERIES PART NUMBERING SCHEME

REV	ECN	APPD
-	3741	JEC 4/21/99
A	3865	JC 11/9/99
B	5354	JT 11/10/03
C	5742	RN 12/28/05



RATINGS

CURRENT - 15A
VOLTAGE - 300V
U.L. FILE NO. EB3421



RATINGS

CURRENT - 15A
VOLTAGE - 300V
CSA FILE NO. LR69703

DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT - 15A
VOLTAGE - 300 V
TUV FILE NO. 20396

CONSULT PCD FOR PART NO. AND
AVAILABILITY OF FOLLOWING OPTIONS:

- CUSTOM COLORS
- CUSTOM MARKING
- CUSTOM KEYING
- SELECTIVE CONTACT LOADING

MATERIALS:

HOUSING: PBT, UL 94 V-0; STANDARD TEMP.
CONTACT: BRASS

MAX OPERATING TEMPERATURE:
105°C


DIMENSIONS

ANSI Y14.5M
UNITS: INCHES
ACAD FILE

TOLERANCES

.XX ±.01
.XXX ±.005
ANGLES ±2°

PROJECTION



Amphenol Pcd

SPECIFICATION DRAWING

ENGR

J. WILKINSON 4/19/99

CHKD

A. PATRIE 4/21/99

APPD

J. CAHALY 4/21/99

TITLE

ELFD SERIES 2-TIER
STACKABLE HEADER
MODULE

ORIGINAL
STAMPED
IN RED

THIS DOCUMENT CONTAINS
PROPRIETARY INFORMATION WHICH
IS THE CONFIDENTIAL PROPERTY
OF AMPHENOL PCD INC. PEABODY, MA

SIZE

A

DWG NO.

ELFD04260


REV

C


CODE: 58982

SCALE: NONE

SHEET 1 OF 2






ELFD04XX0
4 POS HDR




ELFD06XX0
6 POS HDR

L=NUM OF POS X CL SPACING



ELFDXX260
ELFD ASSEMBLY, XX POSITIONS

PRINTED CIRCUIT BOARD CONFIGURATION



RECOMMENDED PCB THICKNESS: .062±.008

SIZE

A

DWG NO.

ELFD04260

REV

C

CODE: 58982

SCALE: NONE

SHEET 2 OF 2