






FCIconnect.com

Copyright FCI


PRODUCT NUMBER
SEE NOTE 1




mat'l. code NOTE 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC				
ltr	ecn no	dr	date	tolerances unless otherwise specified				INCH/MM		title 4 ROW R/A HEADER SOLDER TO BOARD, 1 GP				
C	v13313	MRC	12/19/91	angles linear	.XX ±.01/.3									
D	v23813	MRC	1/07/93		.XXX ±.005/.13									
E	v40228	PDP	1/11/94		.XXXX ±.0020/.051									
F	v50270	SAR	3/10/95	dr	D. SHEAFFER		6/05/91				dwg no 50123		sheet 1 of 2 size A3	
G	v90523	HTB	3/01/99	engr	S. CLARK		6/05/91							
H	v00262	JWS	1/26/00	chr	S. CLARK		6/05/91							
J	M06-0255	AEA	7/06/06	appd	S. CLARK		6/05/91							
sheet index		revision sheet		J	J						type Product Customer Drawing			
				1	2									

form: A3


PRODUCT NUMBER	DIM	LENGTH FORMULAS
SEE NOTE 1	DIM "A"	.100/2.54 x NO. OF COLUMNS + 1.05/26.7
	DIM "B"	.100/2.54 x NO. OF COLUMNS + .750/19.05
	DIM "C"	.100/2.54 x NO. OF COLUMNS DIVIDED BY 2 - .100/2.54



SECTION U-U



SECTION W-W



SECTION X-X


NOTES:

- PRODUCT NUMBERING CODE:
50123 - X YYY Z
TAIL LENGTH (NOTE 5)
NO. OF POSITIONS (NOTE 2)
PLATING (NOTE 4)
BASE NUMBER

PRODUCT NUMBERING CODE FOR
SELECT LOAD PART NUMBERS:

- 50123 - XXYYY
SEQUENCE NUMBER
ALWAYS 'XX'
BASE NUMBER

- THIS PRODUCT IS CONFIGURED IN SIZES OF 20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20,22,24,26,.....118,120,122.
- HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
PIN MATERIAL: PHOS. BRONZE
- PLATING OPTIONS:
1 = 30u"/.76u GOLD
3 = 50u"/1.27u GOLD
5 = 30u"/.76u GXT
- TAIL LENGTH OPTIONS:
H = .180/4.57
J = .120/3.05
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
- FOR DOCUMENTATION MENU, SEE SPEC. BUS-01-057.



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code	surface	tolerance	projection	product family
-	ISO 1302	ISO 406	ISO 1101	HPC
ltr	ecn	no	dr	date
J				
	angles	linear		
	dr	D. SHEAFFER	6/05/91	
	enr	S. CLARK	6/05/91	
	chr	S. CLARK	6/05/91	
	appd	S. CLARK	6/05/91	
sheet	revision			
index	sheet			

