

DATA SHEET

**5063JD series (space miser)
0.25 to 0.40 W; 1% and 5%
Metal film resistors**

Product specification
File under BCcomponents, BC08

2000 Aug 08

Metal film resistors**5063JD series (space miser)
0.25 to 0.40 W; 1% and 5%****DESCRIPTION**

A homogeneous film of metal alloy is deposited on a high grade BALOX ceramic body. After a helical groove has been cut in the resistive layer, tinned connecting wires of electrolytic copper are welded to the end-caps. The resistors are coated with a blue lacquer which provides electrical, mechanical, and climatic protection. The encapsulation is resistant to all cleaning solvents in accordance with "MIL-STD-202E, method 215", and "IEC 60068-2-45".

QUICK REFERENCE DATA

DESCRIPTION	VALUE	
Resistance range	0.22 Ω to 10 M Ω ; see Table 1	
Resistance tolerance and series	$\pm 5\%$, (E24); $\pm 1\%$, (E24/E96)	
Temperature coefficient	$\pm 100 \times 10^{-6}/K$	
Operation mode	normal	long term
Climatic category (LCT/UCT/days)	55/155/56	55/125/56
Max. dissipation, P_{70}	0.40 W	0.25 W
Thermal resistance, R_{th}	200 $^{\circ}C/W$	
Max. continuous operating voltage, U_{max}	200 V (DC or RMS)	
Noise $R \leq 1 M\Omega$	max. 0.1 V/V	
Surface temperature	155 $^{\circ}C$	125 $^{\circ}C$
Operating temperature range	-55 $^{\circ}C$ to +155 $^{\circ}C$	-55 $^{\circ}C$ to +125 $^{\circ}C$
Max. resistance change at P_{70} for resistance range, $\Delta R/R$ max., after:		
1 000 h	0.50%	0.25%
8 000 h	1.0%	0.50%
225 000 h	–	1.5%
Permissible voltage against ambient:		
1 minute	300 V	
continuous	75 V	
Stability ($\Delta R/R$ max.) after:		
load (1000 hours)	$\pm 0.50\% + 0.05 \Omega$	$\pm 0.25\% + 0.05 \Omega$
climatic test	$\pm 1.0\% + 0.05 \Omega$	
resistance to soldering heat	$\pm 0.25\% + 0.05 \Omega$	
short time overload (400 V max.)	$\pm 0.25\% + 0.05 \Omega$	

Metal film resistors

5063JD series (space miser) 0.25 to 0.40 W; 1% and 5%

ORDERING INFORMATION

Table 1 Ordering code indicating resistor type and packaging

TYPE	TC ($\times 10^{-6}/K$)	TOL. (%)	RESISTANCE RANGE	PART NUMBER	SPQ (units)
5063JD	± 100	–	jumper ⁽¹⁾	5063JD0R000J12AFS	5 000; tape & reel
		–	jumper ⁽¹⁾	5063JD0R000J18AFS	5 000; ammpack
		± 5	0.22 to 0.91 Ω	5063JDxxxxxJ12AFS	5 000; tape & reel
		± 5	0.22 to 0.91 Ω	5063JDxxxxxJ18AFS	5 000; ammpack
		± 1	1 Ω to 10 M Ω	5063JDxxxxxF12AF5	5 000; tape & reel
		± 1	1 Ω to 10 M Ω	5063JDxxxxxF18AF5	5 000; ammpack

Note

1. A 0 Ω jumper is available with a maximum resistance $R_{\max} \leq 10 \text{ m}\Omega$ at 3 A.

Composition of the clear text code (NAFTA P/N)

- The resistors have an ordering code starting with 50
- The subsequent digits indicate the resistor type, temperature coefficient, ohmic value, tolerance and packaging; see Table 1
- The ohmic value is represented by 5-digits; see Table 2
- For temperature coefficient and tolerance, see Table 3.

ORDERING EXAMPLE: CLEAR TEXT CODE

The ordering code of a 5063JD resistor, value 5 600 $\Omega \pm 1\%$, taped on a bandolier of 5 000 units in tape on reel is:
5063JD5K600F12AF5.

Table 2 Examples of the ohmic value

OHMIC VALUE	5-DIGIT VALUE
0.22 Ω	0R220
1 Ω	1R000
10 Ω	10R00
100 Ω	100R0
1 k Ω	1K000
10 k Ω	10K00
100 k Ω	100K0
1 M Ω	1M000

Table 3 Letter coding for temperature coefficient and tolerance

TC ($\times 10^{-6}/K$)	LETTER CODE	TOL. (%)	LETTER CODE
100	D	± 5	J
–	–	± 1	F

Metal film resistors

5063JD series (space miser)
0.25 to 0.40 W; 1% and 5%

FUNCTIONAL DESCRIPTION

Product characterization

Standard values of nominal resistance are taken from the E24 or E96 series for resistors with a tolerance of $\pm 5\%$ or $\pm 1\%$.
The values of the E24 series are in accordance with “IEC publication 60063”.

Limiting values



TYPE	LIMITING VOLTAGE ⁽¹⁾ (V)	LIMITING POWER (W)
5063JD	200	0.40

Note

1. The maximum voltage that may be continuously applied to the resistor element, see “IEC publication 60115-1”.


DERATING

The power that the resistor can dissipate depends on the operating temperature; see Figs 1 and 2.



NOISE

The current noise is measured in accordance with “DIN 44049 Part 1 and IEC 600195”. Maximum values are for 99.8% of all resistors; see Fig 3.



Metal film resistors

5063JD series (space miser)
0.25 to 0.40 W; 1% and 5%

Pulse-load behaviour




Fig.4 Pulse on a regular basis; maximum permissible peak pulse power (\hat{P}_{max}) as a function of pulse duration (t_i).




Fig.5 Pulse on a regular basis; maximum permissible peak pulse voltage (\hat{V}_{max}) as a function of pulse duration (t_i).

Metal film resistors

5063JD series (space miser)
0.25 to 0.40 W; 1% and 5%

Definition of symbols (see Figs 4, 5, 6 and 7)

SYMBOL	DESCRIPTION
\hat{P}	applied peak pulse power
\hat{P}_{\max}	maximum permissible peak pulse power; see Fig.4
V_i	applied peak pulse voltage; see Fig 6
\hat{V}_{\max}	maximum permissible peak pulse voltage; see Fig.5
$V(t)$	pulse voltage
R	nominal resistance value
P_U	rated dissipation at ambient temperature
R_{nom}	nominal resistance value
t_i	pulse duration (rectangular pulses)
t_p	pulse repetition time

Pulses

The permissible pulse-load is determined by the resistance change as given for the endurance test after 8000 hours.

PULSE VOLTAGE LIMIT

The maximum permissible impulse voltage \hat{V}_{\max} is the voltage pulse short overload depending on the impulse time t_i . High ohmic values are protected by the interdependence of voltage limit and impulse time. this function is given by

the equation:
$$\hat{V}_{\max} = \frac{2.5 \cdot V_{\max}}{1 + t_i \cdot K} + V_{\max}$$

V_{\max} = maximum permissible continuous voltage;
 t_i = pulse time;
 $K = 100 \text{ s}^{-1}$.

MAXIMUM PULSE-LOAD

The average load \bar{P} must not exceed the rated dissipation. For resistance values above the critical resistance the rated dissipation is given by the resistance value and the limiting

element voltage V_{\max} :
$$\bar{P} = \frac{1}{t_p R} \int_{t_1}^{t_2} U^2(t) dt \leq P_U$$

CONTINUOUS AND SINGLE PULSE-LOAD

There is a difference between repetitive pulse-load ($\bar{P} = \frac{t_i}{t_p} \cdot P$ with P = power at the pulse time t_i) or single pulse load (e.g. switching events $\bar{P} > 0$).

A higher pulse-load P_{\max} is accepted in the latter case.

PULSE SHAPES

Figure 6 shows the maximum pulse-load for a rectangular

pulse shape:
$$\bar{P} = \frac{t_i \cdot \hat{V}^2}{t_p \cdot R}$$

Other pulses should be converted into rectangular pulse shapes (see Fig.7), having the same energy at a given peak voltage. The following equation shows the calculation for exponential pulses:

$$\bar{P} = \frac{\tau_e}{2 \cdot t_p} \cdot \frac{\hat{V}^2}{R} \text{ with } \tau_e = R \cdot C \text{ or } \tau_e = \frac{L}{R}$$




Fig.6 Rectangular pulses.




Fig.7 Exponential pulses.

Metal film resistors

5063JD series (space miser)
0.25 to 0.40 W; 1% and 5%

MECHANICAL DATA

Mass per 100 units

13 g

Marking

The nominal resistance and tolerance are marked on the resistor using four or five coloured bands in accordance with IEC publication 60062 “Colour codes for fixed resistors”.

Mounting

The resistors are suitable for processing on automatic insertion equipment in addition to cutting and bending machines. The minimum bending is 5 mm (.200 inch).

Outlines

The length of the body (L_1) is measured by inserting the leads into holes of two identical gauge plates and moving these plates parallel to each other until the resistor body is clamped without deformation (“IEC publication 60294”).




Table 4 Resistor type and physical dimensions; see Fig.8

TYPE	ØD MAX. (mm)	L ₁ MAX. (mm)	L ₂ MAX. (mm)	Ød (mm)
Dimensions in inches				
5063JD	0.063	.142	1.14	.020
Dimensions in millimetres				
5063JD	1.6	3.6	29	0.5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[BCC5063JD909K1%](#)