

DOLBY B-TYPE NOISE REDUCTION PROCESSOR


■ GENERAL DESCRIPTION

The NJM2063A is the dual low-voltage operating DOLBY B-type noise reduction processor IC. The NJM2036A operates as encode or decode mode and is suitable to the headphone stereo and small cassette tape recorder.


■ FEATURES

- Operating Voltage (1.8V~6V)
- 16 pins, Dual Circuit
- Minimum External Components
- Good temperature characteristics (4mA)
- Internal NR ON/OFF and Mode SW
- Excellent Signal Handling characteristics
- Package Outline DIP16, DMP16
- Bipolar Technology

■ PACKAGE OUTLINE



NJM 2063 AD



NJM 2063 AM

(note) Dolby and the double-D symbol are trademarks of Dolby Laboratories Licensing Corporation, San Francisco, CA94103-4813, USA.

This device available only to licensees of Dolby Lab. Licensing and application information may be obtained from Dolby Lab.

■ ABSOLUTE MAXIMUM RATINGS

(Ta=25°C)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V ⁺	6.5	V
Power Dissipation	P _D	(DIP16) 700 (DMP16) 350	mW
Operating Temperature Range	T _{opr}	-25~+75	°C
Storage Temperature Range	T _{stg}	-55~+150	°C

■ ELECTRICAL CHARACTERISTICS

(V⁺=3.0V, Dolby Level=100mVrms=0dB, Ta=25°C)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Operating Voltage	V ⁺	—	1.8	3.0	6.0	V
Operating Current	I _{CC}	NR ON (ENCODE)	—	8.0	15.0	mA
Voltage Gain	G ₂₃ / G ₁₃₋₁₄	f=1kHz, 0dB	9.0	10.0	11.0	dB
	G ₂₄ / G ₁₅₋₁₃		9.0	10.0	11.0	dB
Total Harmonic Distortion	THD	f=1kHz, ENCODE	—	0.2	0.6	%
Signal Handling	—	V ⁺ =1.8V, f=1kHz, THD<1%	12.0	—	—	dB
S/N Ratio	S/N	R _g =5.6kΩ CCIR/ARM FILTER				
		Encode	64.0	72.0	—	dB
		Decode	—	83.0	—	dB
		NR-OFF	—	74.0	—	dB
N.R Encode Boost 20 log $\frac{V_{3(14)}(N.R ON)}{V_{3(14)}(N.R OFF)}$	ENC-1.4k	f=1.4kHz, V _{3(14)}} (N.R OFF)=-20dB	2.9	4.4	5.9	dB
	ENC-1.4k	f=1.4kHz, V _{3(14)}} (N.R OFF)=-30dB	6.0	7.5	9.0	dB
	ENC-5k	f=5kHz, V _{3(14)}} (N.R OFF)=-20dB	1.7	3.2	4.7	dB
	ENC-5k	f=5kHz, V _{3(14)}} (N.R OFF)=-30dB	6.7	8.2	9.7	dB
	ENC-10k	f=10kHz, V _{3(14)}} (N.R OFF)=0dB	-1.1	0.4	1.9	dB
	ENC-10k	f=10kHz, V _{3(14)}} (N.R OFF)=-40dB	9.8	10.4	11.8	dB

MEMO

[CAUTION]

The specifications on this databook are only given for information, without any guarantee as regards either mistakes or omissions. The application circuits in this databook are described only to show representative usages of the product and not intended for the guarantee or permission of any right including the industrial rights.