



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4205-011.
TUSONIX RoHS COMPLIANT PART NUMBER: 4205-011 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
3. MAX. MOUNTING TORQUE 5 lb.-in. [.265 N-m].

MIN. CAP. (pF)	WORKING VOLTAGE (VWdc)		CURRENT Idc	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85° C	125° C				10 MHz	100 MHz	1 GHz	10 GHz
1500	250	125	15	10 G Ω	500	5	35	60	60

X-2015 Rev-0	REVISION RECORD				--TOLERANCES-- Unless Otherwise Specified		Title		
	Original Release C.O. 5836	0	BLACK COLOR STRIPE ADDED 1500 WAS 2000. L.E. 4-12-91		DECIMAL ± .031 [.79]		BUSHING STYLE EMI FILTER		
	REISSUED 5836	1	RDN TO COMP FMT & ADDED METRIC. S.M. 05-28-02		ANGLES ± 		Drawn	S.M. 05-28-02	Scale 6 X
	20020523-4-02	2	NOTES 1 & 2 ADDED. S.M. 06-09-05		TUSONIX TUCSON, ARIZONA	Approved			J.Mc. 05-28-02
	20050607-1-03	3	ADDED IR & DWV. S.M. 12-01-05			A	4205-011		
				20051102-4-06	4				