


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
--	REVISED	9/8/94	BB
01 ₃	REVISED PER ECN 99-0001	DM 5/19/99	PCW 7/14/99



OUTLINE, -50 AND B/M MUST CARRY
THE SAME REVISION LEVEL

OUTER CONTACT	BERYLLIUM COPPER	GOLD PLATE OVER NICKEL PLATE
CENTER CONTACT	BERYLLIUM COPPER	GOLD PLATE OVER NICKEL PLATE
DIELECTRIC	POLYPROPYLENE, GF	N/A
CABLE: JACKET	FLUORINATED ETHYLENE- PROPYLENE	N/A
SHIELD	SILVER COATED COPPER WIRE, 38 AWG	N/A
DIELECTRIC	PERFLUOROALKOXY OR POLYTETRAFLUOROETHYLENE	N/A
CENTER CONDUCTOR	SILVER COATED COPPER CLAD STEEL	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC DEC ANGLES • 1/64 • .005 • 1°		DRAWN BY BB DATE 10/9/92 CHECKED BY APPROVED BY J. Davis 10/12/92
These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
USE ASSY PROCEDURE NO. A.P. N/A		TITLE OSMT RIGHT ANGLE JACK CABLE PIGTAIL, HIGH TEMPERATURE
SIZE B		CODE IDENT NO. 26805
SCALE 10:1		9952-2200-23
		REV 01 ₃
		SHEET 1 OF 1

ELECTRICAL

Frequency DC - 6 GHz
Nominal Impedance 50 ohms
Voltage Rating 250 Volts (VRMS Max.)
@ Sea Level
VSWR 1.20:1 Max. @ 2GHz
1.40:1 Max. @ 6GHz
Insulation Resistance 1000 Megohms Minimum
Dielectric Withstanding Voltage 500 Volts (VRMS Minimum)
@ Sea Level

MECHANICAL

Connector Durability 100 mating cycles

ENVIRONMENTAL

Temperature Rating -55°C (-67°F) To +150°C (302°F)