

Carflex liquidtight fittings

Straight fittings

For use with Carflex conduit and Carflex X-Flex conduit

Image 1



Assembly

Image 2


Compression
nutFitting
bodyExtended
threadNitrile
rubber
O-ringMetal
locknut

Image 3



Assembly

Image 4

Compression
nutSealing
ring

Ferrule

Fitting
body

O-ring

Plastic
locknut

Features


- Non-conductive and non-corrosive
- Easy to install
- Resistant to oil, acid, ozone and alkaline
- Approved for indoor and outdoor locations
- Listed for "wet locations"
- Nitrile rubber O-ring for a liquidtight termination
- Temperatures up to 107 °C

Specifications



Cat. no.	Size (in.)	Std. ctn. qty.	Std. ctn. wt. (lb)	Dimensions (in.)					Refer to Image
				A	B	C	D	E	
LT43C	3/8	50	3.6	0.55	0.75	1.60	1.30	1.40	1-2
LT43D-NEW	1/2	50	4.2	0.56	0.91	1.62	1.30	1.40	1-2
LT43E-NEW	3/4	50	6.6	0.56	0.91	1.88	1.61	1.71	1-2
LT43F-NEW	1	25	5.5	0.70	1.00	2.20	1.90	2.04	1-2
LT43G	1 1/4	5	1.5	0.71	1.16	2.50	2.17	—	3-4
LT43H	1 1/2	5	2.0	0.75	1.36	2.78	2.43	—	3-4
LT43J	2	5	2.5	1.00	1.45	3.33	—	—	3-4

Diagrams



LT43C-CAR, LT43D-NEW, LT43E-NEW, LT43F

LT43G, LT43H

LT43J

Carflex liquidtight fittings

90° Fittings

For use with Carflex conduit and Carflex X-Flex conduit

Image 1



Assembly

Image 2



Compression nut

Fitting body

Extended thread

Nitrile rubber O-ring

Metal locknut

Image 3



Assembly

Image 4



Compression nut

Sealing ring

Ferrule

Fitting body

O-ring

Plastic locknut

Features

- Non-conductive and non-corrosive
- Easy to install
- Resistant to oil, acid, ozone and alkaline
- Approved for indoor and outdoor locations
- Listed for “wet locations”
- Nitrile rubber O-ring for a liquidtight termination
- Temperatures up to 107 °C

Specifications



Cat. no.	Size (in.)	Std. ctn. qty.	Std. ctn. wt. (lb)	Dimensions (in.)							Refer to Image
				A	B	C	D	E	F	G	
LT20C	¾	50	3.6	0.56	1.44	1.44	1.56	1.39	1.26	–	1–2
LT20D-NEW	½	50	4.2	0.56	1.76	2.05	1.62	1.40	1.30	1.15	1–2
LT20E-NEW	¾	50	6.6	0.56	2.04	2.35	1.88	1.71	1.61	1.50	1–2
LT20F-NEW	1	25	5.5	0.70	2.01	2.01	2.26	2.04	1.90	–	1–2
LT20G	1¼	5	1.5	0.75	2.50	3.55	2.48	–	–	–	3–4
LT20H	1½	5	2.0	0.75	2.80	3.98	2.77	–	–	–	3–4
LT20J	2	5	2.5	0.94	3.48	4.56	3.33	–	–	–	3–4

Diagrams

