

Bearing type: ◎=Ball "B" ※=Sleeve "S" ○=1B1S "B(S)" ●=Hypro bearing "X"

PHOTO	Frame size (mm)	Model No.	Bearing Type	Voltage (v)	Current (A)	Power (W)	Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	Noise (dB/A)	Weight (g)
	40X40X10	AD0412HB-G70(T)	◎ ※ ●	12	0.10	1.20	6000	0.191	6.70	0.1	2.54	25.0	14
		AD0412MB-G70(T)	◎ ※ ●	12	0.08	0.96	4800	0.162	5.70	0.078	1.98	20.0	
		AD0412LB-G70(T)	◎ ※ ●	12	0.07	0.84	4200	0.134	4.70	0.060	1.52	14.0	
		AD0412HB-G71	◎ ※ ●	12	0.10	1.20	6000	0.191	6.70	0.1	2.54	25.0	
		AD0412MB-G71	◎ ※ ●	12	0.09	1.08	4800	0.162	5.70	0.078	1.98	20.0	
		AD0412LB-G71	◎ ※ ●	12	0.08	0.96	4200	0.134	4.70	0.060	1.52	14.0	
		AD0424HB-G70(T)	◎ ※ ●	24	0.09	2.16	6000	0.191	6.70	0.1	2.54	25.0	
		AD0424MB-G70(T)	◎ ※ ●	24	0.08	1.92	4800	0.162	5.70	0.078	1.98	20.0	
		AD0424LB-G70(T)	◎ ※ ●	24	0.07	1.68	4200	0.134	4.70	0.060	1.52	14.0	
	40X40X15	AD0412HB-D50	◎ ●	12	0.12	1.44	8000	0.240	8.53	0.249	6.23	39.3	27
		AD0412MB-D50	◎ ●	12	0.10	1.20	7000	0.209	7.40	0.185	4.63	31.8	
		AD0412LB-D50	◎ ●	12	0.08	0.96	6000	0.179	6.37	0.142	3.55	30.3	
		AD0412HB-D52	◎ ●	12	0.15	1.80	8000	0.240	8.53	0.249	6.23	39.3	
		AD0412MB-D52	◎ ●	12	0.12	1.44	7000	0.208	7.40	0.185	4.63	31.8	
		AD0412LB-D52	◎ ●	12	0.10	1.20	6000	0.179	6.37	0.142	3.55	30.3	
	40X40X20	AD0405HB-C50	◎ ※ ●	5	0.29	1.45	7800	0.253	8.97	0.300	7.49	31.9	28
		AD0405MB-C50	◎ ※ ●	5	0.16	0.80	6500	0.219	7.78	0.246	6.15	27.0	
		AD0405LB-C50	◎ ※ ●	5	0.14	0.70	6000	0.197	7.00	0.188	4.71	23.9	
		AD0412UB-C50	◎ ※ ●	12	0.14	1.68	8500	0.270	9.60	0.331	8.27	36.1	
		AD0412HB-C50	◎ ※ ●	12	0.10	1.20	7800	0.253	8.97	0.300	7.49	31.9	
		AD0412MB-C50	◎ ※ ●	12	0.08	0.96	6900	0.219	7.78	0.246	6.15	28.5	
		AD0412LB-C50	◎ ※ ●	12	0.07	0.84	6200	0.197	6.99	0.188	4.71	25.0	
		AD0424HB-C50	◎ ※ ●	24	0.09	2.16	7800	0.253	8.97	0.300	7.49	31.9	
		AD0424MB-C50	◎ ※ ●	24	0.07	1.68	6900	0.219	7.78	0.246	6.15	28.5	
	40X40X28	AD0412UB-B31	◎	12	0.23	2.76	10000	0.386	13.50	0.478	11.99	42.5	38
		AD0412HB-B31	◎	12	0.22	2.64	9000	0.344	12.13	0.391	9.77	38.8	
		AD0412MB-B31	◎ ※	12	0.18	2.16	7500	0.274	9.60	0.232	5.81	36.5	
		AD0412DB-B31	◎ ※	12	0.07	0.84	4500	0.169	5.90	0.094	2.34	19.2	
		AD0424UB-B31	◎ ※	24	0.23	5.52	13000	0.488	17.22	0.741	18.83	49.7	
		AD0424HB-B31	◎ ※	24	0.12	2.88	8100	0.344	12.13	0.391	9.77	36.2	
	45x45x06	AD4505LB-K90(S)	○	5	0.10	0.50	4500	0.169	5.98	0.059	1.48	23.3	11
		AD4505MB-K90(S)	○	5	0.09	0.45	5500	0.211	7.43	0.085	2.13	26.5	
		AD4505HB-K90(S)	○	5	0.14	0.70	6200	0.237	8.36	0.108	2.69	33.0	
		AD4505LX-K90	●	5	0.10	0.50	4300	0.169	5.98	0.059	1.48	23.0	
		AD4505MX-K90	●	5	0.09	0.45	5000	0.211	7.43	0.084	2.10	25.5	
		AD4505HX-K90	●	5	0.14	0.70	6000	0.237	8.36	0.108	2.69	32.6	
		AD4512LB-K90(S)	○	12	0.08	0.96	4500	0.169	5.98	0.059	1.48	23.3	
		AD4512MB-K90(S)	○	12	0.09	1.08	5500	0.211	7.43	0.085	2.13	26.5	
		AD4512HB-K90(S)	○	12	0.10	1.20	6200	0.237	8.36	0.108	2.69	33.0	
		AD4512LX-K90	●	12	0.08	0.96	4300	0.169	5.98	0.059	1.48	23.0	
		AD4512MX-K90	●	12	0.09	1.08	5000	0.211	7.43	0.084	2.10	25.5	
		AD4512HX-K90	●	12	0.10	1.20	6000	0.237	8.36	0.108	2.69	32.6	
PHOTO	Frame size (mm)	Model No.	B S B(S) X Bearing Type	Voltage (v)	Current (A)	Power (W)	Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	Noise (dB/A)	Weight (g)

Specifications subject to change without notice.