

Not Recommended for New Designs

This product was manufactured for Maxim by an outside wafer foundry using a process that is no longer available. It is not recommended for new designs. The data sheet remains available for existing users.

A Maxim replacement or an industry second-source may be available. Please see the QuickView data sheet for this part or contact technical support for assistance.

For further information, [contact Maxim's Applications Tech Support](#).



5V/3.3V/3V 2A Step-Down, PWM, Switch-Mode DC-DC Regulators

General Description

The MAX727/MAX728/MAX729 are monolithic, bipolar, pulse-width modulation (PWM), switch-mode, step-down DC-DC regulators. Each is rated at 2A. Very few external components are needed for standard operation because the power switch, oscillator, feedback, and control circuitry are all on-chip. Employing a classic buck topology, these regulators perform high-current step-down functions.

These regulators have excellent dynamic and transient response characteristics, while featuring cycle-by-cycle current limiting to protect against overcurrent faults and short-circuit output faults. They also have a wide 8V to 40V input range.

Each regulator is available in a 5-pin TO-220 package. These devices have a preset 100kHz oscillator frequency and a preset current limit of 2.6A. See the MAX724/MAX726 data sheet for more applications information.

Applications

Distributed Power from High-Voltage Buses
High-Current, High-Voltage Step-Down Applications
Multiple-Output Buck Converter

Features


- ♦ Input Range: Up to 40V
- ♦ 2A On-Chip Power Switch
- ♦ Fixed Outputs: 5V (MAX727)
3.3V (MAX728)
3V (MAX729)
- ♦ 100kHz Switching Frequency
- ♦ Excellent Dynamic Characteristics
- ♦ Few External Components
- ♦ 8.5mA Quiescent Current
- ♦ TO-220 Package

Ordering Information

PART	TEMP. RANGE	PIN-PACKAGE
MAX727CCK	0°C to +70°C	5 TO-220
MAX727ECK	-40°C to +85°C	5 TO-220
MAX728CCK	0°C to +70°C	5 TO-220
MAX728ECK	-40°C to +85°C	5 TO-220
MAX729CCK	0°C to +70°C	5 TO-220
MAX729ECK	-40°C to +85°C	5 TO-220


MAX727/MAX728/MAX729

Typical Operating Circuit



Pin Configuration

FRONT VIEW



5-PIN TO-220

CASE IS CONNECTED TO GROUND. STANDARD PACKAGE HAS STAGGERED LEADS. CONTACT FACTORY FOR STRAIGHT LEADS.



Maxim Integrated Products 1

Call toll free 1-800-998-8800 for free samples or literature.

5V/3.3V/3V 2A Step-Down, PWM, Switch-Mode DC-DC Regulators

ABSOLUTE MAXIMUM RATINGS

Input Voltage	45V
Switch Voltage with Respect to Input Voltage	50V
Switch Voltage with Respect to GND Pin (V_{SW} negative)	
(Note 1)	35V
SENSE Pin Voltage	-0.3V, +10V
Operating Temperature Ranges	
MAX72_CCK	0°C to +70°C
MAX72_ECK	-40°C to +85°C

Junction Temperature Ranges:

MAX72_CCK	0°C to +125°C
MAX72_ECK	-40°C to +125°C
Storage Temperature Range	-65°C to +160°C
Lead Temperature (soldering, 10sec)	+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

($V_{IN} = 25V$, $T_J = T_{MIN}$ to T_{MAX} , unless otherwise noted.)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
Input Supply Voltage Range		8.0		40.0	V
Switch-On Voltage (Note 2)	$I_{SW} = 0.5A$			1.2	V
	$I_{SW} = 2A$			1.7	
Switch-Off Leakage	$V_{IN} = 25V$, $V_{SW} = 0V$			150	μA
	$V_{IN} = 40V$, $V_{SW} = 0V$			250	
Supply Current (Note 3)	$V_{IN} \leq 40V$, $V_{SENSE} = 5.5V$		8.5	11	mA
Minimum Supply Voltage	Normal Mode		7.3	8.0	V
	Start-Up Mode (Note 4)	$T_J \geq 0^\circ C$	3.5	4.8	
		$T_J < 0^\circ C$	3.5	5.0	
Switch-Current Limit (Note 5)		2.0	2.6	3.2	A
Maximum Duty Cycle		85	90		%
Switching Frequency	$T_J = +25^\circ C$	90	100	110	kHz
	$T_J \leq +125^\circ C$	85		120	
	$V_{OUT} = V_{SENSE} = 0V$ (Note 5)		20		
Switching Frequency Line Regulation	$8V \leq V_{IN} \leq 40V$		0.03	0.10	%/V
Error-Amplifier Voltage Gain	$1V \leq V_C \leq 4V$		2000		V/V
Error-Amplifier Transconductance		3000	5000	9000	μmho
Error-Amplifier Source Current	$V_{SENSE} = V_{OUT} - 10\%$	100	140	225	μA
Error-Amplifier Sink Current	$V_{SENSE} = V_{OUT} + 10\%$	0.6	1.0	1.7	mA

5V/3.3V/3V 2A Step-Down, PWM, Switch-Mode DC-DC Regulators

ELECTRICAL CHARACTERISTICS (continued)

($V_{IN} = 25V$, $T_j = T_{MIN}$ to T_{MAX} , unless otherwise noted.)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
SENSE Voltage	$V_C = 2V$	MAX727	4.85	5.00	5.15
		MAX728	3.20	3.30	3.40
		MAX729	2.90	3.00	3.10
SENSE Pin Divider Resistance	$T_j = +25^{\circ}C$	MAX727	3.0	5.0	8.0
		MAX728	2.5	4.2	7.0
		MAX729	2.2	3.8	6.5
Output Voltage Tolerance	V_{OUT} (nominal) = 5V (MAX727), 3.3V (MAX728), or 3V (MAX729); all conditions of input voltage, output voltage, and load current	$T_j = +25^{\circ}C$	± 0.5	± 2.0	%
		$T_j = T_{MIN}$ to T_{MAX}	± 1.0	± 3.0	
Output Voltage Line Regulation	$8V \leq V_{IN} \leq 40V$		0.005	0.020	%/V
V_C Voltage	0% duty cycle	$T_j = +25^{\circ}C$	1.5		V
V_C Voltage Temperature Coefficient	0% duty cycle	$T_j = T_{MIN}$ to T_{MAX}	-4		mV/ $^{\circ}C$
Thermal Resistance Junction to Case (Note 6)				4.0	$^{\circ}C/W$

Note 1: Do not exceed switch-to-input voltage limitation.

Note 2: For switch currents between 1A and 2A, maximum switch-on voltage can be calculated via linear interpolation.

Note 3: By setting the SENSE pin to 5.5V, the V_C pin is forced to its low clamp level and the switch duty cycle is forced to zero, approximating the zero load condition.

Note 4: For proper regulation, total voltage from V_{IN} to GND must be $\geq 8V$ after start-up.

Note 5: To avoid extremely short switch-on times, the switch frequency is internally scaled down when V_{SENSE} is less than 2.6V (MAX727), 2.0V (MAX728), or 1.8V (MAX729). Switch current limit is tested with V_{SENSE} adjusted to give a 1 μ s minimum switch-on time.



Note 6: Guaranteed, not production tested.

Pin Description

PIN	NAME	FUNCTION
1	SENSE	SENSE Input is the internal error amplifier's input, and should be directly connected to V_{OUT} . SENSE also aids current limiting by reducing oscillator frequency when V_{OUT} is low.
2	V_C	Error-Amplifier Output. A series RC network connected to this pin compensates the MAX727/MAX728/MAX729. Output swing is limited to about 5.8V in the positive direction and -0.7V in the negative direction. V_C can also synchronize the MAX727/MAX728/MAX729 to an external TTL clock in the 115kHz to 170kHz range. See MAX724/MAX726 data sheet.
3	GND	Ground requires a short, low-noise connection to ensure good load regulation. The internal reference is referred to GND, so errors at this pin are multiplied by the error amplifier.
4	V_{SW}	Internal Power Switch Output. The switch output can swing 35V below ground and is rated for 2A.
5	V_{IN}	V_{IN} supplies power to the internal circuitry and also connects to the collector of the internal power switch. V_{IN} must be bypassed with a low-ESR capacitor, typically 200 μ F or 220 μ F.

5V/3.3V/3V 2A Step-Down, PWM, Switch-Mode DC-DC Regulators

Package Information



Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

4 Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 (408) 737-7600

© 1995 Maxim Integrated Products

Printed USA

MAXIM is a registered trademark of Maxim Integrated Products.