




REVISIONS				DOC. NO. SPC-FD05, Total Pages: 2			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
129	A	RELEASED	DJC	3/10/98	JJC	3/13/98	JMM



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 335 VRMS @ SEA LEVEL
FREQUENCY RANGE: 0-6 GHz
INSERTION LOSS: ≤ .1 dB MAX/1 GHz
VSWR: 1.3 MAX @ 6 GHz
FOR RG-174, 188, 188A, 316/U, ALPHA 9174, 9316,
BELDEN 8216, 83269, 83284, 84316 & TIMES LMR-100 CABLE

6	FERRULE	1	COPPER	NICKEL
5	HOUSING	1	BRASS	NICKEL
4	DIELECTRIC	1	TEFLON	NONE
3	DIELECTRIC	1	TEFLON	NONE
2	PIN	1	BRASS	GOLD
1	BODY	1	BeCu	NICKEL
ITEM	DESCRIPTION	QTY	MATERIAL	FINISH



SUGGESTED STRIPPING INSTRUCTIONS
SUGGESTED CRIMP DIES: .130
PIN TO BE SOLDER

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.



SPC TECHNOLOGY

DRAWING TITLE: MCX CRIMP PLUG				DRAWING FILE 92N3359.DWG			
DRAWN BY: DANIEL CAREY				DATE: 3/10/98			
CHECKED BY: JOHN COLE				DATE: 3/13/98			
APPROVED BY: JEFF MCVICKER				DATE: 7/7/98			
SCALE: NTS				SHEET: 1 OF 1			