



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC., ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	06/19/01	MCCORMICK
B	ECN#2084: CHANGED DESIGN OF SMA COUPLER	05/19/05	M.LAHEY
C	ECN 3124: UPDATE DWG FORMAT	12/19/07	D.GRIFFIN
.	.	.	.

2X GOLD PLATED
CENTER CONTACT




2X SMA JACK



Ø.21 [5.33]


2X .250-36 THREAD

2X TEFLON INSULATOR



NOTES:
1. MATERIAL: NICKEL PLATED BRASS

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] ANGLES ±2° .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / - 0 > 60 [1524] +5% / -0%	APPROVALS		DATE		L-com CONNECTIVITY PRODUCTS	01845	
	DRAWN BY MCCORMICK		06/06/01			CATEGORY COAXIAL	
	CHECKED BY D.PARHAM		06/06/01			PRODUCT DESCRIPTION COUPLER SMA F/SMA F	
	APPROVED BY R.CARRICK		06/19/01				
	PROJ 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			SIZE A	FSCM NO. 43321
				SCALE: NONE		CAD FILE: BA23.SLDDRW	SHEET 1 OF 1