

90584	***26	26	(35.53)/1.399	(31.75)/1.250	(30.48)/1.200
	***24	24	(32.99)/1.299	(29.21)/1.150	(27.94)/1.100
	***22	22	(30.45)/1.199	(26.67)/1.050	(25.40)/1.000
	***20	20	(27.91)/1.099	(24.13)/.950	(22.86)/.900
	***18	18	(25.37)/.999	(21.59)/.850	(20.32)/.800
	***16	16	(22.83)/.899	(19.05)/.750	(17.78)/.700
	***14	14	(20.29)/.799	(16.51)/.650	(15.24)/.600
	***12	12	(17.75)/.699	(13.97)/.550	(12.70)/.500
	***10	10	(15.21)/.599	(11.43)/.450	(10.16)/.400
	***08	8	(12.67)/.499	(8.89)/.350	(7.62)/.300
	***06	6	(10.13)/.399	(6.35)/.250	(5.08)/.200
90584	***04	4	(7.59)/.299	(3.81)/.150	(2.54)/.100
PART NO.	CCT SIZE	DIMENSION A	DIMENSION B	DIMENSION C	

HOUSING

MATL. POLYESTER, RATED UL 94V-0, COLOUR WHITE.

IDT CONTACT

MATL : PHOSPHOR BRONZE (0.28)/.011 REF THICK.

PLATING : (2-4um) / 80-160u" TIN

NOTES:

1. APPL. CLASS TO DIN 40040 HME (-25°C/+100°C)

2. PRODUCT SPECIFICATION: PS-99020-0011

3. WIRE TERMINATION SPEC: ES-99033-0002

4. PACKAGING SPEC: PK-90584-001

90584- * * * *

04 TO 26 = CKT SIZE.



3= NO CIRCUITS VOIDED.

4= CIRCUITS 4 & 5 VOIDED.

1= INDIVIDUAL TUBED ASSY

2= STACKED TUBED ASSY - SEE SHEET 2

9= NON STANDARD OPTION - SEE SHEET 3



ADDED PACKAGING NOTE. EC NO: IPG2013-2038 DRAWN BY: JBYRNE CHK'D BY: CHIKDISHA APPR: STGRFF IN DATE: 2013/06/26 DATE: 2013/06/27 DATE: 2013/07/16	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY DMCNAMAR	DATE 2003/09/01	TITLE 1.27MM PF LOW PRO IDT BOARD-IN CONNECTOR				
			4 PLACES	± ---	± ---	CHECKED BY BMAGUIRE	DATE 2003/09/01					
			3 PLACES	± ---	± .010	APPROVED BY MWILHITE	DATE 2003/09/01	MOLEX INCORPORATED				
			2 PLACES	± 0.25	± ---	MATERIAL NO. SEE CHART						
			1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

90584	***26	26	(35.53)/1.399	(31.75)/1.250	(30.48)/1.200
	***24	24	(32.99)/1.299	(29.21)/1.150	(27.94)/1.100
	***22	22	(30.45)/1.199	(26.67)/1.050	(25.40)/1.000
	***20	20	(27.91)/1.099	(24.13)/.950	(22.86)/.900
	***18	18	(25.37)/.999	(21.59)/.850	(20.32)/.800
	***16	16	(22.83)/.899	(19.05)/.750	(17.78)/.700
	***14	14	(20.29)/.799	(16.51)/.650	(15.24)/.600
	***12	12	(17.75)/.699	(13.97)/.550	(12.70)/.500
	***10	10	(15.21)/.599	(11.43)/.450	(10.16)/.400
	***08	8	(12.67)/.499	(8.89)/.350	(7.62)/.300
	***06	6	(10.13)/.399	(6.35)/.250	(5.08)/.200
90584	***04	4	(7.59)/.299	(3.81)/.150	(2.54)/.100
PART NO.	CCT SIZE	DIMENSION A	DIMENSION B	DIMENSION C	

HOUSING

MATL. POLYESTER, RATED UL 94V-0, COLOUR WHITE.

IDT CONTACT

MATL : PHOSPHOR BRONZE (0.28)/.011 REF THICK.

PLATING : (2-4um) / 80-160u" TIN

NOTES:

1. APPL. CLASS TO DIN 40040 HME (-25°C/+100°C)

2. PRODUCT SPECIFICATION: PS-99020-0011

3. WIRE TERMINATION SPEC: ES-99033-0002

4. PACKAGING SPEC: PK-90584-001

90584- * * * *

04 TO 26 = CKT SIZE.



3= NO CIRCUITS VOIDED.

4= CIRCUITS 4 & 5 VOIDED.

1= INDIVIDUAL TUBED ASSY

2= STACKED TUBED ASSY - SEE SHEET 2

9= NON STANDARD OPTION - SEE SHEET 3



ADDED PACKAGING NOTE. EC NO: IPG2013-2038 DRAWN BY: JBYRNE CHK'D BY: CHIKDISHA APPR: STGRFF IN DATE: 2013/06/26 DATE: 2013/06/27 DATE: 2013/07/16	DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY DMCNAMAR	DATE 2003/09/01	TITLE 1.27MM PF LOW PRO IDT BOARD-IN CONNECTOR				
				4 PLACES	± ---	± ---	CHECKED BY BMAGUIRE					DATE 2003/09/01
				3 PLACES	± ---	± .010	APPROVED BY MWILHITE	DATE 2003/09/01	MOLEX INCORPORATED			
				2 PLACES	± 0.25	± ---	DOCUMENT NO. SDA-90584					
1 PLACE		± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				