

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14						
			A1	REVISED PER ECR 10-006882	05APR10	JR	TM

D

C

B

A



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
12-10 AWG STRANDED	12-10 AWG STRANDED	NOT CERTIFIED

- 1 STAMP 5S AMP 12-10* APPROX AS SHOWN
5S INDICATES STUD SIZE
- 2 PHOS BRONZE PER ASTM B-103, ANNEALED
- 3 TIN PLATE 0.00254 [0.000100] MIN
THK PER ASTM B545

53013

B

A

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-12-93	 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
			CHK DA PATTERSON 2-12-93					
VOLTAGE RATING: N/A	DIMENSIONS: MM[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 2-12-93	NAME				
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED		0 PLC ± -	PRODUCT SPEC	TERMINAL, SHORT SPRING SPADE, BUDGET -				
		1 PLC ± -	-					
		2 PLC ± -	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		3 PLC ± -	-	A2	00779	C-53013	-	
		4 PLC ± -	FINISH	WEIGHT	SCALE			SHEET
	MATERIAL	ANGLES ± -	CUSTOMER DRAWING	10:1			1 of 1	A1
	- 2	- 3						