

Single-Phase Basic PDU 3.8kW 40A, two independent 20A 120V circuits, 0U Vertical mount, 40 5-15/20R outlets, two L5-20P / 5-20P inputs

MODEL NUMBER: PDU40TDUAL



Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories. Dual independent power circuits offer all the benefits of two PDUs in a single housing, ideal for network equipment fitted with dual redundant input cables.

Features

- 40A total single phase 120V Basic Power Distribution Unit / PDU with dual independent 120V 20A circuits (Agency de-rated to 16A per circuit)
- Functions as two PDUs built into a single 70 in. / 1778mm 0U vertical rackmount housing
- Color coded circuit identification with separate black and gray colored outlets, circuit breakers and line cords
- 40 NEMA 5-15/20R outlets (20 black / 20 gray)
- Two 10 ft. / 3m NEMA L5-20P / 5-20P compatible inputs (1 black / 1 gray)
- Two 20A circuit breakers (1 black / 1 gray)
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications

Specifications

OVERVIEW	
Style	Vertical Rackmount, Wallmount, Raceway, Workbench
PDU Type	Basic
OUTPUT	

Highlights

- Basic single phase dual circuit 40A 120V PDU
- Functions as two 20A PDU systems in a single housing
- Two 10 ft. / 3m NEMA L5-20P / 5-20P compatible inputs
- 40 NEMA 5-15/20R outlets (20 per circuit)
- 70 in. / 1778mm 0U vertical rackmount installation

Applications

- Ideal means of powering servers and networking equipment with dual redundant power supplies and other applications requiring numerous outlets, high capacity and a compact form factor

Package Includes

- 70 inch dual circuit 120V 20A PDU
- Mounting hardware
- Set of two NEMA L5-20R to NEMA 5-20P plug set adapters
- Manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output Capacity Details	3.8kW total, 1.9kW per circuit (120V input); 4.0kW total, 2.0kW per circuit (127V input); 3.2kW total, 1.6kW per circuit (100V input), 40A maximum total, 20A maximum per circuit (Agency de-rated to 32A continuous total, 16A continuous per circuit)
Frequency Compatibility	50 / 60 Hz
Output (Watts)	4800
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	40A
Outlet Quantity / Type	40 NEMA 5-15/20R
Number of Outlets	40
Outlet Type	NEMA 5-15R, NEMA 5-20R
INPUT	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	40
Maximum Input Amps Details	20A maximum per circuit (Agency de-rated to 16A per circuit continuous)
PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Phase	Single-Phase
PHYSICAL	
Shipping Dimensions (hwd / in.)	5 x 2.25 x 71.25
Shipping Dimensions (hwd / cm)	12.7 x 5.7 x 181
Shipping Weight (lbs.)	10
Shipping Weight (kg)	4.5
Unit Dimensions (hwd / in.)	70 x 1.5 x 3
Unit Dimensions (hwd / cm)	177.8 x 3.8 x 7.6
Unit Weight (lbs.)	9
Unit Weight (kg)	4.1
Material of Construction	Aluminum
Form Factors Supported	Zero U vertical rackmount, wallmount, raceway, workbench and more
PDU Form Factor	Vertical (0U)
CERTIFICATIONS	
Certifications	Tested to UL60950-1, RoHS compliant
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	2-year limited warranty
-------------------------------------	-------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.