



Part Number: 1533R

CAT5e Horizontal, 4pr, F/UTP, PVC Jkt, CMR

Product Description

CAT5e (100MHz), 4-Pair, F/UTP-foil shielded, Riser-CMR, Premise Horizontal cable, 24 AWG solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield, PVC jacket, RJ-45 compatible

Technical Specifications

Product Overview

Environmental Space:	Riser
Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 100MHz Category 5e

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
AWG Size:	24

Insulation

Material
PO - Polyolefin

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.260 in	No

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
9.38 Ohm/100m	5 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	15 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
@ 100 MHz 537.6 ns/100m	45 ns/100m	70 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	65.3 dB	62.3 dB	63.3 dB	60.3 dB	63.8 dB	60.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	52.2 dB	49.2 dB	51.8 dB	48.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	46.0 dB	43.0 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43.8 dB	40.8 dB	43.8 dB	40.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
16 MHz	8.2 dB/100m	47.2 dB	44.2 dB	39.0 dB	36.0 dB	39.7 dB	36.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	36.5 dB	33.5 dB	37.8 dB	34.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	33.9 dB	30.9 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	31.2 dB	28.2 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm
62.5 MHz	17.0 dB/100m	38.4 dB	35.4 dB	21.4 dB	18.4 dB	27.9 dB	24.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm
100 MHz	22.0 dB/100m	35.3 dB	32.3 dB	13.3 dB	10.3 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm
155 MHz	28.1 dB/100m	32.4 dB	29.4 dB	4.4 dB	1.4 dB	20.0 dB	17.0 dB	18.8 dB		
200 MHz	32.4 dB/100m	30.8 dB	27.8 dB			17.8 dB	14.8 dB	18.0 dB		

Voltage

UL Voltage Rating
300V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	30 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.0 in
Min Bend Radius/Installation:	2.25 in

Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class D
CPR Euroclass:	Eca
Data Category:	Category 5e
ANSI Compliance:	S-90-661-2012 Category 5e, ANSI/NEMA WC-63.1 Category 5e
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 5e
IEEE Specification:	POE per 802.3af & POE+ per 802.3at-2009
Third Party Performance Verification:	Category 5e

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL 1666 Riser
------------------	---------------

Part Number

Plenum (Y/N):	No
Plenum Number:	1533P

Variants

Item #	Color	Footnote
1533R 0101000	BLACK	C
1533R 010A1000	BLACK	
1533R 0061000	BLUE	C
1533R 006A1000	BLUE	
1533R F2V1000	GRAY	C
1533R F2V1640	GRAY	C
1533R F2VA1000	GRAY	
1533R 0051000	GREEN	C
1533R 005A1000	GREEN	C
1533R 0031000	ORANGE	C
1533R 003A1000	ORANGE	C
1533R 0021000	RED	C
1533R 002A1000	RED	C
1533R 0041000	YELLOW	C
1533R 004A1000	YELLOW	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	http://www.belden.com/p

Product Notes

Notes:	Values above 100 MHz are for Engineering Information Only. Shield is Bonded to Jacket Inner Wall for Electrical Stability. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.