





LOC		DIST		REVISONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
O		REV PER EC 0512-0319-04		01JUN2005	BC	GS	
A		REV PER EC 0512-0302-05		13DEC2005	BC	GS	



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
RECOMMENDED PRINTED CIRCUIT BOARD
THICKNESS 1.27
COMPONENT SIDE OF PRINTED CIRCUIT BOARD

- 1 GLASS FILLED POLYESTER, BLACK
- 2 PHOSPHOR BRONZE
- 3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101 PERFORMANCE LEVEL 2.
- 4 DATUMS ESTABLISHED BY CUSTOMER.
- 5 DRILLED HOLE DIAMETER 0.700±0.025
COPPER THK 0.025-0.05
TIN THICKNESS 0.004-0.01
- 6 DIMENSION ESTABLISHED BY CUSTOMER.
- 7 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1.27µm MIN NICKEL AND ACTION PIN: 0.5µm MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER

5120641-1
PART
NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: B. CARBO 01JUN2005		EGR: G. SKIPPER 01JUN2005		APVD: G. SKIPPER 01JUN2005		NAME: RECEPTACLE ASSEMBLY, SIGNAL/GROUND COMBINATION, 72 POSITION, RIGHT HAND, Z-PACK 12 HM	
mm		9 PLC ±		PRODUCT SPEC		APPLICATION SPEC		SIZE: CAGE CODE DRAWING NO		RESTRICTED TO	
		1 PLC ±		WEIGHT		CUSTOMER DRAWING		A 00779 C=5120641		SCALE 5:1 SHEET 1 OF 1 REV A	
MATERIAL		FINISH		HOUSING: 1		CONTACTS: 3 7					
CONTACTS: 2											