





NOTES
1 - LINEAR MEASURE $\frac{mm}{IN}$, OR mm/IN
2 - mm DIMENSIONS ARE FOR REFERENCE ONLY
3 - TERMINALS ARE PLATED FOR SOLDERING
4 - METRIC MOUNTING HOLES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS	
OPERATING FORCE	170 - 398 GR MAX 6 - 14 OZ
RELEASE FORCE	113 GR MIN 4 OZ
DIFFERENTIAL TRAVEL	0,15 - 0,41 .006 - .016
OVERTRAVEL	1,01 MIN .040
RELEASE TRAVEL	0,18 MIN .007
FREE POSITION	.625 MAX

ELECTRICAL DATA	
CONTACT ARRANGEMENT S P D T	
L83 15.1A 1/2HP 125, 250 VAC 1/2A 125 VDC, 1/4A 250 VDC 5A 125 VAC "L"	



SCALE FULL			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±			
DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/104	X
ONE PLACE	X,X	0,47/016	X,X
TWO PLACES	X,X,X	0,167/006	X,X,X
THREE PLACES	X,X,X,X	0,067/015	X,X,X,X
ANGLES		0,137/005	
SI METRIC		US CUSTOMARY	
DESIGN UNITS			
RAW MATERIAL - COMMERCIAL STANDARD			
MICRO SWITCH STANDARDS APPLY			
DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED			
WEIGHT			