



Enclosure Material	: Aluminium
Body Colour	: Unfinished
External Height - Imperial	: 1.22"
External Height - Metric	: 31mm
External Width - Imperial	: 2.19"
External Width - Metric	: 55.5mm
External Depth - Imperial	: 1.61"
External Depth - Metric	: 41mm
IP Rating	: 65
Highest NEMA Rating	: 4

Technical drawing of a rectangular metal enclosure with dimensions in inches and millimeters. The drawing includes a top view, a front view, and two cross-sections (A-A and B-B). The top view shows a rectangular frame with dimensions 200 (7.874) x 188 (7.402). The front view shows a rectangular box with dimensions 200 (7.874) x 188 (7.402) x 120 (4.724). Cross-section A-A shows the internal structure with dimensions 188 (7.402) x 120 (4.724). Cross-section B-B shows the internal structure with dimensions 200 (7.874) x 120 (4.724). The drawing also includes a detail of the corner fasteners, showing four (4) M4 X 32 Flat Head Screws. The drawing is labeled 'Section A-A', 'Section B-B', and 'Section C-C'.

Dimensions (inches in parentheses):

- Top View: 200 (7.874), 188 (7.402), 176 (6.929), 174.48 (6.869), 138 (5.433), 22 (0.866), 74.13 (2.918), 96 (3.465), 90 (3.543), 108 (4.252), 112.48 (4.428), 120 (4.724).
- Front View: 200 (7.874), 188 (7.402), 171.20 (6.740), 171.20 (6.740), 188 (7.402), 189.20 (7.449), 200 (7.874), 120 (4.724), 109.20 (4.299), 108 (4.252), 71.20 (2.803).
- Section A-A: 188 (7.402), 120 (4.724), 108 (4.252), 71.20 (2.803), 75 (2.953), 10 (0.394).
- Section B-B: 200 (7.874), 120 (4.724), 108 (4.252), 71.20 (2.803), 75 (2.953), 10 (0.394).
- Section C-C: 188 (7.402), 120 (4.724), 108 (4.252), 71.20 (2.803), 75 (2.953), 10 (0.394).
- Detail: 4 (4) M4 X 32 Flat Head Screws, 20 (0.787), 1.80 (0.071), 0.90 (0.126), 0.480 (0.189) X 4PCS.

Tolerances: ± 0.30 (± 0.04)


Tolerances : ± 0.30 (± 0.012)

Dimensions : Millimetres

Box Diecast



G155




Tolerances : $\pm 0.30 (\pm 0.012)$

Dimensions : Millimetres

Box Diecast





G105



Tolerances : ± 0.30 (± 0.012)




Dimensions : Millimetres

[illegible]

62.60 (2.465)

Ø 4.80(0.189) X 2PCS

52.40 (2.063)




Dimensions : Millimetres

Box Diecast




G118



Tolerances : $\pm 0.30 (\pm 0.012)$

Dimensions : Millimetres

G112



Tolerances : ± 0.30 (± 0.012)

Dimensions : Millimetres

Part Number Table

Description	Part Number
Box, Diecast, 31 × 55.5 × 41mm	G105
Box, Diecast, 52 × 79.6 × 74.6mm	G110
Box, Diecast, 25.5 × 102.5 × 52.5mm	G112
Box, Diecast, 60 × 175 × 80mm	G118
Box, Diecast, 75 × 200 × 120mm	G123
Box, Diecast, 90.5 × 260 × 160mm	G155

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.