



Home: >

Part Number: 67665-0014

0.5 18P PLUG (COVER UP) L/F

Image not available

Status: **OBsolete**
Replacement: Contact Molex
Series: 67665
Category: Molex Parts

[CHECK DISTRIBUTOR INVENTORY](#) [Add to My Parts](#)[Go to Part Detail ▾](#)

Series image - Reference only

Product Environmental Compliance[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active [Product Compliance Statement](#) [EU RoHS Certificate of Compliance \(PDF\)](#) [Multiple Part Product Compliance Statements](#)

EU RoHS, REACH SVHC, & Low-Halogen

[Multiple Part Industry Compliance Documents](#)

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail**[COLLAPSE ALL](#) **General**

Status	Obsolete
Category	Molex Parts
Series	<u>67665</u>
UPC	756054389454

Physical

Net Weight	1.160/g
------------	---------

PRODUCTS**QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas
Application Tooling
Cable Assemblies
Connected Lighting
Connectors
Copper Flex
Electrical Products
Industrial Automation
Membrane Switches
Optical Solutions
Printed Electronic Solutions

Company Information
Contact Molex
Cross-Reference
Koch Industries
Industries
Investor Relations
Literature
Molex Racing
Press Room / Press Releases
Product Index
Sitemap
Terms & Conditions

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Feedback | Help
Jobs
Legal | Trademarks
Mobile Site
Supplier Portal
Privacy Policy
Tradeshows

