


DRAWING MADE IN AMERICAN PROJECTION

© 1970 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.FOR .080 TO .125 WIRE INS. DIA
TONGUE MATERIAL THK .031 ± .002MARKING 22-18 FOR MILITARY
COMMERCIAL RANGE 22-16

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	0	NPS.70-0110 (REV.2)	12-9-70	FCY
	A	REVISED P-6600 WM	6-17-71	FCY
	B	SLEEVE COLOR CORRECTED RED WAS BLUE	2-3-72	FCY
	C	REV. PER ECN PC-5578	8-7-72	FCY
	D	REVISED PER ECN F-598	10-17-72	FCY
	E	ADD -2 P85-0448	3/5/55	FCY
	F	REVISED G-3044	4-12-58	49
	G	OBSOLETE -2 PER G-3785	10/10/88	FG
	H	REV PER G-5648	1/21/91	DKS/TME
	J	REV. / 0720-0043-93	6-12-93	MLC
	K	REVISED PER ECR-06-000293	4/11/06	jrr/TJM

QTY	PACKAGE TYPE	PART NO
	LOOSE PIECE	52411
5,000	ON TAPE, REEL	52411-1
1,000	ON TAPE, LG. BOX	52411-2
100	LOOSE PC. BOX	8-52411-1

OBSOLETE

8-52411-1	
52411-2	
52411-1	INSULATION: NYLON COLOR: RED
52411	SLEEVE: COPPER (QQ-C-576)
	BODY: PHOSPHOR BRONZE (QQ-B-750)
	- TIN PL. (MIL-T-10727)
PART NO.	MATERIAL & FINISH
	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
CONTRACT NO. 12-2-70	NAME WIRE TERMINAL
DR. J. E. Gunning	P.I.D.G.-SPRING SPADE
CHK. J. E. Gunning	WIRE SIZE: 22-16
APPD. J. E. Gunning	SIZE B CODE IDENT NO. 00779
REL. J. E. Gunning	NUMBER 52411
DSGN APPD.	SCALE NTS
OTHER APPD.	SHEET 1 OF 1

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES
TOLERANCES ON:
DECIMALS ±.008
ANGLES ± 5°

MATERIAL

SEE TABLE

CONTRACT NO. 12-2-70

DR. J. E. Gunning

CHK. J. E. Gunning

APPD. J. E. Gunning

REL. J. E. Gunning

DSGN APPD.

OTHER APPD.

AMP

AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

NAME WIRE TERMINAL

P.I.D.G.-SPRING SPADE

WIRE SIZE: 22-16

SIZE B CODE IDENT NO. 00779

NUMBER 52411

SCALE NTS

SHEET 1 OF 1

CUSTOMER DRAWING