

M DTE6-2RN281

DRAWING
 NUMBER


8

ISSUE

REVISIONS

A	53191-D	18NOV05	BP	CHECK
B	C055989	18NOV05	BP	CHECK
C	C054958	18NOV05	BP	CHECK
D	C072661	18NOV05	BP	CHECK
E	CO-77179B	18NOV05	BP	CHECK
F	0016895	18NOV05	BP	CHECK
G	0018962	18NOV05	BP	CHECK

MBF 5 JUNE 67
 DRAWN
 L S D
 CHECK
 14FEB06



NOTE —

- 1 — 4-40 UNC X .125 REF TERMINAL SCREW AND LOCKWASHER(3)
- 2 — ROLLER LEVER BRACKET ASSEMBLY MAY BE SET AT ANY POSITION AROUND AXIS OF PLUNGER
- 3 — SEAL RATING : NEMA 1.3
IP 54

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE — — — 3 LB MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE — — — 6 OZ MIN	-L59- 10 A-125 OR 250 VAC	UNLESS OTHERWISE NOTED
PRETRAVEL — — — .312 MAX	0.5 A-125 VDC; 0.15 A-250 VDC	DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL — — .165 MAX		TOLERANCES ARE:
OVERTRAVEL — — — .219 MIN		ONE PLACE (.0) ± .030
		TWO PLACE (.00) ± .015
		THREE PLACE (.000) ± .008
		ANGLES ±
SWITCH-BASIC REPLACEMENT - DT-2R3-A7		WEIGHT .71 LB