



Hash Chokes LA6



INDUCTANCES 3.35 μ H to 1,000 μ H



PART NUMBER	INDUCTANCE $\pm 20\%$ (μ H)	DC RESISTANCE OHMS MAXIMUM (W)	DC CURRENT MAX (A)	COIL DIAMETER	LEAD WIRE SIZE (A WG)	LEAD LENGTH MIN (INCHES)	BODY LENGTH MAX (INCHES)	REFER TO FIGURE	CORE MATERIAL
MEASURED ON 1kHz BRIDGE									
LA6-3R35M	3.35	.01	20	.60	12	1.25	1.25	A	Ferrite
LA6-4R9M	4.9	.016	15	.60	14	1.25	1.25	A	Ferrite
LA6-8R8M	8.8	.021	10	.56	16	1.25	1.25	A	Ferrite
LA6-4R0M	4	.012	8	.38	20	1.25	0.875	B	Ferrite
LA6-400M	40	.082	3	.31	20	1.25	1.25	C	Ferrite
LA6-680M	68	.054	5	.56	20	1.25	1.25	D	Ferrite
LA6-101M	100	.216	2.0	.38	20	1.25	1.25	E	Ferrite
LA6-125M	125	.080	3.5	.50	20	1.25	1.25	D	Ferrite
LA6-251M	250	.170	2.5	.44	20	1.25	1.25	D	Ferrite
LA6-501M	500	.260	2.0	.44	20	1.25	1.25	D	Ferrite
LA6-102M	1000	.550	1.0	.50	20	1.25	1.25	D	Ferrite