



"X" = NOT TOOLED	MATERIAL NUMBER	CONNECTOR SIZE	NUMBER OF CIRCUITS	RETENTION PEG OPTION	DIM. "B"
	43090-0003	8	8	NO	.350/(8.89)
X	43090-0004	8	8	YES	.350/(8.89)
	43090-0005	8	10	NO	.450/(11.43)
X	43090-0006	8	10	YES	.450/(11.43)



- NOTES:
- 1) MATERIALS :
HOUSING - POLYESTER, GLASS-FILLED, UL94V-0, COLOR - BLACK
TERMINALS - .015/(0.38) THICK PHOSPHOR BRONZE
 - 2) FINISH :
SELECT GOLD IN CONTACT AREA: 50 MICROINCHES MIN.,
*SELECT TIN IN PC TAIL AREA: 100 MICROINCHES MIN.,
WITH OVERALL NICKEL UNDERPLATE: 50 MICROINCHES MIN.,
*THE PRIMARY SHIPPING CARTON WILL BE LABELED 'COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC; CARTONS WITHOUT THIS LABEL MAY CONTAINS TIN-LEAD IN THE PC TAIL.
 - 3) PRODUCT SPECIFICATION : PS-42878
 - 4) CONNECTORS ARE SHIPPED IN THERMOFORMED TRAYS, PER PACKAGING SPECIFICATION PK-42878-492.
 - 5) THIS MODULAR JACK CAVITY CONFORMS TO, AND ACCEPT PLUGS WHICH CONFORM TO, F.C.C. RULES AND REGULATIONS PART 68.5, SUBPART 'F'.
 - 6) THIS MODULAR JACK IS DESIGNED FOR USE WITH .047/(1.19) THICK P.C. BOARDS.
 - 7) THIS MODULAR JACK MUST BE CAPABLE OF FITTING INTO MOLEX GAGE G-42410.
 - 8) THESE DIMENSIONS APPLY WHEN RETENTION PEG OPTION IS PRESENT.


2	E
1	E1
SH	REV

ADD 'NOT TOOLED' EC NO: UCP2005-2408 DRW: NLSCHMDT 2005/05/12 CHKD: ELHAG 2005/05/12 APPR: FSMITH 2005/05/12	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY		
		▽ - 0 ▽ - 0	mm INCH	DIMENSION STYLE IN/MM		DRAWN BY DATE MUELLER 1998/08/10 CHECKED BY DATE ROBERTS 1998/08/11 APPROVED BY DATE R EDGLEY 1998/08/11	TITLE LOW PROFILE, 8/8 & 8/10 VERTICAL MODJACK W/ .165/(4.20) RADIUS-ASSY MOLEX MOLEX INCORPORATED SEE CHART SDA-43090-****	DOCUMENT NO.	SHEET NO. 1 OF 2
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							



RECOMMENDED P.C. BOARD LAYOUT

8 POSITION MODULAR JACK BODY LOADED
WITH 8 TERMINALS IS SHOWN ABOVE



RECOMMENDED P.C. BOARD LAYOUT

8 POSITION MODULAR JACK BODY LOADED
WITH 10 TERMINALS IS SHOWN ABOVE

SEE SHEET ONE EC NO: UCP2004-1617 DRAWN:LSCHMDT 2004/03/03 CHKD:LSCHMDT 2004/03/03 APPR:FSMITH 2004/03/03	DESCRIPTION	QUALITY SYMBOLS ▽ = 0 ▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	REVISE ON CAD ONLY			
				mm	INCH	DIMENSION STYLE				TITLE LOW PROFILE, 8/8 & 8/10 VERTICAL MODJACK W/ .165/(4.20) RADIUS-ASSY  MOLEX INCORPORATED	
						IN/MM					
			4 PLACES	± ---	± ---	DRAWN BY					DATE
			3 PLACES	± ---	± .010	MUELLER					1998/08/10
			2 PLACES	± 0.25	± .015	CHECKED BY	DATE				
			1 PLACE	± 0.38	± ---	ROBERTS	1998/08/11				
			ANGULAR ±1/2°		APPROVED BY	DATE	MATERIAL NO.	DOCUMENT NO.	SHEET NO.		
			DRAFT WHERE APPLICABLE		R EDGLEY	1998/08/11	SEE CHART	SDA-43090-****	2 OF 2		
			MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						