

The main logo for the advertisement, featuring the word 'Wiss' in a large, bold, italicized sans-serif font, followed by a registered trademark symbol (®).

- Aviation & Tinner's Snips
- HVAC Tools
- Scissors & Shears
- Utility Knives

Wiss® products have been earning their reputation for craftsmanship and long life since 1848. One result: Wiss has been the market leading “call-out brand” for aviation snips for over 50 years. The wide product line includes scissors, industrial shears, utility knives, siding and HVAC tools... all with famous Wiss quality built in.

Wiss® Table of Contents

Contents	Page No.
Snips introduction	247
Aviation snips	248 - 250
All-purpose cutters	250 - 251
Tinners' snips	252 - 254
Heating, ventilating and air conditioning tools (HVAC)	255 - 258
Ratcheting Pipe Cutters	258
Vinyl siding tools	259
Utility knives	260 - 261
Snap knife	261
Replacement utility knife blades	261
Shears and scissors introduction	262
Stainless steel scissors and shears	262 - 263
Solid steel trimmers	264
Industrial shears	264 - 267
Inlaid shears and trimmers	264
Belt and leather cutting scissors	267
Double rounded scissors and shears	267
Pinking shears	268
Sewing and embroidery scissors	268
Quick-Clip® lightweight speed cutters	269
Special purpose Industrial snips and shears	270 - 271
Electrician's scissors	272
Wiss Numerical Index	273

Key to symbol




Wiss® Aviation Snips

The Wiss® line of aviation snips is the most complete line on the market. Wiss® aviation snips are advanced metal cutting tools originally developed for cutting extremely tough alloys used in the aircraft industry. Wiss® snips are widely used in the construction trades by general contractors, HVAC professionals, sheet metal workers, drywallers, roofers, electricians, and siding contractors. They are common tools for maintenance specialists and industrial workers, and can be found in almost any industrial application. Wiss® snips offer superior cutting performance required of conventional snips to handle acute angles, complex patterns and circular shapes in galvanized steel up to 18 gauge (.049"). The M5R bulldog snip is recommended for galvanized steel up to 16 gauge (.065").

The jaws of Wiss® aviation snips are made of durable and wear-resistant special molybdenum steel. This provides the extra service demanded by the compound lever action and withstands the severe strain of cutting heavy stock or tight curves.


Wiss® also offers a comprehensive range of tinner's snips in various sizes. These are made from drop-forged steel, each tool features polished jaws for smooth action, cleaner cutting, and larger handle rings for increased comfort and performance.



Snips selection chart

To find the proper snips for your requirements, check the chart below. Simply find your requirements in the listing. The applicable snips are indicated in the chart.

	Wiss® M1R, M2R M3R, & M300	Wiss® M6R, M7R	Wiss® M4R	Wiss® Tinner's Snips A & V Series	Wiss® MPC3	Wiss® M5R	Wiss® Special Series M1RS1 & M2RS1	Wiss® Industrial Snips W Series
Do-it-yourselfer	•	•	•	•	•			•
Roofer	•	•		•				•
Automotive	•	•		•			•	•
Drywallers	•	•						•
Plumber	•	•		•				•
HVAC	•	•	•	•		•	•	•
Electrician	•	•		•				•
Industrial/MRO	•	•		•	•			•
WISS® SNIPS FOR SPECIAL JOBS								
Notching & Nibbling Heavy Stock						•		•
Cutting Curves	•	•					•	•
Double Cut-Snips			•					
Cutting Titanium Inconel, Inconel X, & Stainless Steel								•



M1R, M2R & M3R Aviation Snips



Left Cut, Cuts left from tight curves to straight
M1R



Right Cut, Cuts right from tight curves to straight
M2R




Straight Cut, Cuts straight and slight curves
M3R

- Non-slip serrated jaw of tough molybdenum steel holds material firmly and uniformly spreads cutting force across blade edge
- Withstands strain of cutting heavy stock

- Spring-action for fast, effortless feed
- Handles made of high tensile strength alloy steel that exceeds hand power limit
- Non-slip, textured grips and safety latch

Cat. No.	UPC No.	Grip color	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
			Inch	mm				oz	g	
M1R	037103580122	Red	9 3/4	248	1 3/8	35	18 Gauge Steel	84	2381	6
M2R	037103580184	Green	9 3/4	248	1 3/8	35	18 Gauge Steel	84	2381	6
M3R	037103580214	Yellow	9 3/4	248	1 1/2	38	18 Gauge Steel	84	2381	6

M1RS1, M2RS1 Special Series Aviation Snips



Cuts left and straight
M1RS1



Cuts right and straight
M2RS1

- Non-slip serrated jaw of tough molybdenum steel allows for compound lever action
- Jaws specially hardened to cut metals such as stainless steel, inconel, and titanium

- Withstands strain of cutting heavy stock and tight curves
- Handles made of high tensile strength alloy steel that exceeds hand power limit
- Non-slip, textured grips and safety latch

Cat. No.	UPC No.	Grip color	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
			Inch	mm				oz	g	
M1RS1	037103580139	Blue	9 3/4	248	1 3/8	35	18 Gauge Stainless Steel	84	2381	6
M2RS1	037103580191	Blue	9 3/4	248	1 3/8	35	18 Gauge Stainless Steel	84	2381	6

M5R Bulldog Aviation Snips

- For notching or trimming extra heavy stock up to 16 gauge
- Non-slip, serrated jaw made of tough molybdenum steel allows for compound lever action
- Withstands strain of cutting heavy stock
- Handles made of high tensile strength alloy steel that exceeds hand power limit
- Handy hang-up hole
- Non-slip, textured grips and safety latch



Cat. No.	UPC No.	Grip color	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
			Inch	mm				oz	g	
M5R	037103580252	Red	9 1/4	233	7/8	22	16 Gauge Steel (0.65"/1.65mm)	70	1985	6

M6R, M7R Offset Aviation Snips



- Offset blades keep hands clear of metal
- Non-slip serrated jaw of tough molybdenum steel holds material firmly and uniformly spreads cutting force across blade edge
- Withstands strain of cutting heavy stock and tight curves



- Spring-action for fast, effortless feed
- Handles made of high tensile strength alloy steel that exceeds hand power limit
- Handy hang-up hole
- Non-slip, textured grips and safety latch

Cat. No.	UPC No.	Grip color	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
			Inch	mm				oz	g	
M6R	037103583376	Red	9 1/4	233	1 1/4	32	18 Gauge Steel (0.049"/1.22mm)	84	2381	6
M7R	037103583383	Green	9 1/4	233	1 1/4	32	18 Gauge Steel (0.049"/1.22mm)	84	2381	6

Repair Parts for Aviation Snips

Cat. No.	UPC No.	Description	Shelf Pack
P406	037103580924	Replacement Spring for M1R, M3-R, M5R, M7R, M8R (10 pack)	10
P407	037103580931	Replacement Spring for M2R, M6R, M9R (10 pack)	10

M8R & M9R Vertical Aviation Snips



Left Cut, Cuts left from tight curves to straight

M8R



**NEW
PRODUCT**



Right Cut, Cuts right from tight curves to straight

M9R




- Vertical offset blades keep hands clear of material
- Ideal for increased reach in overhead projects or ground-level cutting
- Cuts low carbon cold rolled steel and other heavy gauge materials
- Non-slip serrated jaw blades help grip material to minimize slip

- Handles made of high tensile strength alloy steel that exceeds hand power limit
- Handy hang-up hole
- Safety latch aids in tool storage and secures tool when not in use

Cat. No.	UPC No.	Grip color	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
			Inch	mm				oz	g	
M8R	037103224552	Red	10 7/8	276	1 3/4	45	22 Gauge Steel	16.48	487	6
M9R	037103224576	Green	10 7/8	276	1 3/4	45	22 Gauge Steel	16.48	487	6

M4R Pipe & Duct Cutting Snips



- Cuts any shape ducts, seams, sheet metal stock, vinyl tiles and plastic laminates
- Jaw action automatically adjusts blade clearance for squarer, cleaner cuts
- Handles made of high tensile strength alloy steel that exceeds hand power limit
- Non-slip, textured grips and safety latch

Cat. No.	UPC No.	Grip color	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
			Inch	mm				oz	g	
M4R	037103240989	Gray	9 1/4	233	9/16	14	20 Gauge Steel	73	2084	1

MPC3 Multipurpose Snips



- Cuts straight and slight curves
- Used for cutting screening, hardware cloth, synthetic shingles, tile gutters, downspouts, and carpeting
- Non-slip serrated jaw helps grip material to minimize slipping
- Non-slip, textured grips and safety latch

Cat. No.	UPC No.	Length		Inch	mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
MPC3	037103580221	9	229	1 3/8	35	20 Gauge Steel	72	2041	6

See page 249 for repair parts for all aviation snips. When ordering these parts, please identify model number of snip.

MPX All-purpose Cutter

- 3" serrated blades for general use
- Serrated blades help hold material while cutting
- Compound action provides easy cutting
- Chrome-plated blades resist rust and corrosion
- Spring loaded for faster opening
- Textured grips
- Small closed position handle design for smaller hands



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
MPX	037103190635	10 1/2	267	3		76	72	2041	6

M300 Long Cut Aviation Snips

- 3" cutting blade designed for performance cutting
- Combines the long cut of tinners snips with compound action
- Compound action multiplies the cutting force
- Great for making long, fast cuts in sheet metal, aluminum, and much more
- Cuts up to 20 gauge steel
- Serrated jaws and non-slip textured grips



Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
M300	037103126481	10 1/2	267	3		76	20 Gauge Steel	72	2041	6

M400 Long Cut Offset Aviation Snips

- Long offset blades with 3" cut, help keep material away from hands
- Compound action design multiplies the cutting force for added performance and easier use
- Cuts up to 20 gauge low carbon cold rolled steel, aluminum and plastic
- Blade serrations aggressively grips material when cutting
- Non-slip grips provide control when cutting
- Safety latch keeps tool closed for storage


**NEW
PRODUCT**



Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
M400	037103224606	12 1/8	308	3		76	20 Gauge Steel	16	473	6

Solid Steel Tinner’s Snips

- Traditional tools of the sheet metal trades
- Wiss® Tinner’s Snips are available in both straight pattern and in duckbill combination pattern
- Wiss® Industrial Snips are industrially used and have for years set the professional standard for incomparable ruggedness, durability, and efficiency
- Superior cutting properties and durability offers extraordinary edges for high performance
- A complete selection of sizes is available in both patterns
- Wiss® Tinner’s Snips are made from hot drop-forged steel



Straight Pattern Tinner’s Snips



- Cuts straight and wide curves
- Used in plumbing, heating, air conditioning and roofing trades
- Blades hand edged for maximum cutting efficiency
- Flat face guides tool along straight line
- Blades of quality steel, hot drop-forged for sharp edge and long life
- Rust resistant blades
- Double-dipped cushion grip for all-weather comfort and better grip

Cat. No.	UPC No.	Length				Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
A13N	037103213907	7	178	1 3/4	44	24 Gauge	88	2500	6
A12N	037103213914	8 1/4	209	2	51	24 Gauge	113	3200	6
A11N	037103213921	9 3/4	248	2 1/4	57	24 Gauge	159	4500	6
A10N	037103213891	11	279	2 1/2	63	22 Gauge	168	4750	6
A9N	037103213938	12 1/2	317	3	76	20 Gauge	215	6100	6

Duckbill Combination Pattern Snips

- Cuts moderately tight curves left or right
- Blades hand edged for maximum cutting efficiency
- Blades of quality steel, hot drop-forged for sharp edge and long life
- Rust resistant blades
- Double-dipped cushion grip for all-weather comfort and better grip



V19N

Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
V10N	037103213945	10 1/4	260	2 1/4		57	24 Gauge	152	4300	6
V19N	037103213990	13	330	3		76	22 Gauge	215	6100	6

Straight Pattern

- Used for straight cuts and wide curves
- Blades hand edged for maximum cutting efficiency
- Flat face guides tool along straight line
- Blades of quality steel, hot drop-forged for sharp edge and long life
- Rust resistant blades
- Double-dipped cushion grip for all-weather comfort and better grip

Industrial use



Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
W7N	037103213969	14 1/2	368	4		100	18 Gauge	44	1250	1

Bulldog Pattern

- Industrial use
- Longer handles and wider head provide high leverage
- Greater cutting power for notching, nibbling and chopping heavy stock
- Blades hand edged for maximum cutting efficiency
- Blades of quality steel, hot drop-forged for sharp edge and long life
- Rust resistant blades
- Double-dipped cushion grip for all-weather comfort and better grip



Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
W5N	037103213976	16 1/2	419	2 1/2		63	16 Gauge Steel	59	1665	1

Offset/Bent Pattern Snip



- Offset blades keeps hands clear of metal
- Blades are hot drop-forged and precision ground for sharp cutting edge and long life

Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
W7BWN	037103213983	14 1/4	362	4		100	18 Gauge (0.049"/1.22mm)	44	1250	1

12" Lightweight Aluminum Handle Snip



- 3" cut length
- Sleek head design reduces cutting effort by allowing easy flow of material while cutting
- Slim nose, ideal for making cuts in tight places and reaching tight corners
- Large, wide handle loops increase cutting leverage and comfortably fit all hand sizes, including gloved hands
- Strong & durable lightweight aluminum construction
- Easy and quick blade replacement

Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
W12L	037103239983	12	305	3		76	22 Gauge	69	1950	4

14" Lightweight Aluminum Handle Snip



- 3-1/4" cut length
- Sleek head design reduces cutting effort by allowing easy flow of material while cutting
- Large, wide handle loops increase cutting leverage and comfortably fit all hand sizes, including gloved hands
- Longer handle length and rounded head design improve cutting leverage
- Strong & durable lightweight aluminum construction
- Easy and quick blade replacement

Cat. No.	UPC No.	Length		Inch		mm	Recommended max. capacity low carbon cold rolled steel	Pack Wt.		Shelf Pack
		Inch	mm					oz	g	
W14L	037103239976	14	356	3 1/4		82.5	22 Gauge	94	2676	4

Replacement Blade Kits

Cat. No.	UPC No.	Description	Shelf Pack
W12LRB	037103240965	Blade replacement kit for W12L - Includes 2 snap in blades, 1 center pivot bolt, 1 washer, and 1 locknut	1
W14LRB	037103240958	Blade replacement kit for W14L - Includes 2 snap in blades, 1 center pivot bolt, 1 washer, and 1 locknut	1

Heating, Ventilating and Air Conditioning Tools

- Traditional tools of the sheet metal trades
- Made from quality steel for long life
- Treated industrial finish helps prevent rust
- Cushion grip handles for all-weather comfort and grip

3" Hand Seamer

- Used to bend and flatten sheet metal
- 3 1/4" jaw width and 1-1/4" maximum seam depth
- Raised 1/4" depth marking for clear visibility
- Strong & durable forged blades that make accurate & consistent bends
- Optimal handle span for maximum power & comfortable operating range
- Non-slip cushion grips for superior comfort and control



**NEW
PRODUCT**

Cat. No.	UPC No.	Jaw Depth		Jaw Width		Length		Pack Wt.		Shelf Pack
		Inch	mm	Inch	mm	Inch	mm	oz	g	
WS3	037103240026	1/4 – 1 1/4	6 – 30	3 1/4	83	9 1/4	235	69	1950	3

3" Offset Hand Seamer

- Used to bend and flatten sheet metal
- Ideal for working in confined areas & able to be used in wide range of bending applications
- 3-1/4" jaw width and 1-1/4" maximum seam depth
- Raised 1/4" depth marking for clear visibility
- Optimal handle span for maximum power & comfortable operating range
- Non-slip cushion grips for superior comfort and control



**NEW
PRODUCT**

Cat. No.	UPC No.	Jaw Depth		Jaw Width		Length		Pack Wt.		Shelf Pack
		Inch	mm	Inch	mm	Inch	mm	oz	g	
WS4	037103240033	1/4 – 1 1/4	6 – 30	3 1/4	83	9	229	71	2018	3

6" Hand Seamer

- Used to bend and flatten sheet metal
- Used for making longer, & more uniform folds
- Requires less strokes & reduces bowing of metal
- 6" jaw width and 1-1/4" maximum seam depth
- Raised 1/4" depth marking for clear visibility
- Strong & durable forged blades that make accurate and consistent bends
- Optimal handle span for maximum power & comfortable operating range
- Non-slip cushion grips for superior comfort and control



**NEW
PRODUCT**

Cat. No.	UPC No.	Jaw Depth		Jaw Width		Length		Pack Wt.		Shelf Pack
		Inch	mm	Inch	mm	Inch	mm	oz	g	
WS6	037103239990	1/4 – 1 1/4	6 – 30	6	152	9 1/4	235	65	1837	2

5-Blade Hand Crimper – 1 5/8" Throat Depth

**NEW
PRODUCT**



- Commonly used to crimp round metal pipe
- Produces long, shallow crimps that form tight fitting connection between pipes
- Optimal handle span for comfortable operating range and power, but still maintains a shallow crimp that does not concave pipe & obstruct airflow
- Non-slip cushion grips for superior comfort and control

Cat. No.	UPC No.	Throat Depth		Length		Pack Wt.		Shelf Pack
		Inch	mm	Inch	mm	oz	g	
WC5L	037103239921	1 5/8	41	10	254	53	1497	3

5-Blade Hand Crimper – 1 1/4" Throat Depth

**NEW
PRODUCT**



- Commonly used for crimping downspouts & guttering
- Produces tight fitting crimps that form leak resistant connections and does not deform downspouts
- Optimal handle span for comfortable operating range and power
- Non-slip cushion grips for superior comfort and control

Cat. No.	UPC No.	Throat Depth		Length		Pack Wt.		Shelf Pack
		Inch	mm	Inch	mm	oz	g	
WC5S	037103239891	1 1/4	32	9 1/2	241	50	1406	3

3-Blade Hand Crimper – 1 1/4" Throat Depth

**NEW
PRODUCT**



- Used for crimping heavier gauge pipe
- Optimal handle span for comfortable operating range and power
- Non-slip cushion grips for superior comfort and control

Cat. No.	UPC No.	Throat Depth		Length		Pack Wt.		Shelf Pack
		Inch	mm	Inch	mm	oz	g	
WC3S	037103239891	1 1/4	32	9 1/2	241	45	1270	3

Folding Tools

- Commonly used for folding channels & making long uniform bends in sheet metal
- All 3 sizes have 3/8" & 1" depth folding channel
- Sight holes are positioned along each folding channel to ensure proper depth alignment
- Constructed of heavy 16 gauge steel that keeps folding channels from widening and ensures precise and accurate bends
- 12" folding tool is ideal for folding drive cleat channels with 3/8" depth and using 1" depth to make longer, wider folds in register boots, end caps, plenums, etc.
- 18" & 24" tools are ideal for making long, uniform folds



Cat. No.	UPC No.	Description	Folding Channel Depths		Pack Wt.		Shelf Pack
			Inch	mm	oz	g	
WF12	037103239945	12" Folding Tool	3/8 & 1	9.5 – 25	86	2427	4
WF18	037103239952	18" Folding Tool	3/8 & 1	9.5 – 25	130	3697	4
WF24	037103239938	24" Folding Tool	3/8 & 1	9.5 – 25	172	4876	4

Hand Notcher

- Cuts 30° V shaped cut in sheet metal
- Gives clean notch without slipping at corners and take-off tabs
- Non-slip cushion grips for superior comfort and control



Cat. No.	UPC No.	Cutting Angle	Throat Depth		Length		Pack Wt.		Shelf Pack
			Inch	mm	Inch	mm	oz	g	
WHN1	037103239969	30°	13/16	21	8 3/4	222	50	1406	3

Cable Tie Tensioning Tool

- For tightening nylon ties when securing flex duct to take-off collars
- Installs both heavy & light duty cable ties
- Easy to operate cut-off mechanism that trims excess cable strap
- Comfortable cushion grip handles & internal handle stop



Cat. No.	UPC No.	Cable Tie Width	Length		Pack Wt.		Shelf Pack
			Inch	mm	oz	g	
WT1	037103240019	3/8" & thinner	7 1/2	191	86	2449	6

Ratcheting Pipe Cutters



- Ideal for working in tight spaces where traditional cutting tools will not work
- Cuts brass, copper, aluminum, PVC, and other thin-walled conduit material
- Cutting wheel rotates around pipe, while handle ratchet only needs to move as little as 10 degrees
- Nylon fiberglass frame construction for durability
- Extra cutting wheel storage in handle of medium and large versions for convenience and quick change out.
- Extra cutting wheel included with medium & large versions

Cat. No.	UPC No.	Description	Pipe Cutting Diameter		Pack Wt.		Shelf Pack
			Inch	mm	oz	g	
WRPCSM	037103222428	Small Ratcheting Pipe Cutter	1/8 – 1/2	3 – 13	28.16	811	3
WRPCMD	037103222435	Medium Ratcheting Pipe Cutter	1/4 – 7/8	6 – 23	38.72	1098	3
WRPCLG	037103222442	Large Ratcheting Pipe Cutter	5/16 – 1 1/8	8 – 29	38.72	1098	3
Replacement Parts							
WRPCWH1	037103223654	Replacement Cutting Wheel for Small Ratcheting Pipe Cutter, 2 Pack					6
WRPCWH2	037103223661	Replacement Cutting Wheel for Medium and Large Ratcheting Pipe Cutters, 2 Pack					6

Snap Lock Punch Tool

- Forms raised projections, or tabs, to secure vinyl siding, aluminum siding, or plastic skirting to finishing trim
- 3/8" throat
- Vinyl handle grips for added comfort

**NEW
PRODUCT**



Cat. No.	UPC No.	Description	Length		Pack Wt.		Shelf Pack
			Inch	mm	oz	g	
WSP1	037103241016	Snap Lock Punch Tool	11	276	48	1367	4

Trim Nail Punch

- Provides proper setting depth for nailing soffit, fascia, and trim without denting surface
- Long nose allows easy access to 1/2" J channel
- Accommodates up to 1 1/4" standard trim
- Textured surface for better grip
- Will not dent surface

**NEW
PRODUCT**



Cat. No.	UPC No.	Description	Length		Pack Wt.		Shelf Pack
			Inch	mm	oz	g	
WTNP1	037103241030	Trim Nail Punch	9	225	40	1134	4

Siding Removal Tool

- Used to pull out damaged vinyl siding
- Offset handle to keep hand/ knuckles safely above work surface
- Vinyl grip for extra comfort
- One piece steel design for smooth, consistent unlocking

**NEW
PRODUCT**



Cat. No.	UPC No.	Description	Length		Pack Wt.		Shelf Pack
			Inch	mm	oz	g	
WSR1	037103241009	Siding Removal Tool	9	225	31	590	4

Wiss® Utility Knives and Replacement Blades

- Wiss® offers a complete line of knives and replacement blades for DIY, professional and industrial uses
- Replacement blade styles include the standard sharp point heavy duty, extra heavy-duty, round point and hook styles
- All knife handles are designed for maximum comfort and usability
- Most knives come with three blades (except where noted below)

Quick-Change Folding Blade Utility Knife



- Patent-pending quick-change blade mechanism. Thumb release for easy blade removal and replacement.
- Folding design lets blade recess completely into handle
- Single-hand operation with interchangeable thumb pin and belt-clip
- Comfortable, non-slip grip with anodized aluminum housing
- Stainless steel belt clip for faster access (interchangeable)
- Accepts most .025" steel utility knife blades including round point and hook blades

Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
WKFQ4R	037103222206	Quick-Change Folding Blade Utility Knife	5	20

Quick-Change Comfort Grip Utility Knife



- Retractable utility knife with 8 positions
- Quick change blade release and reload
- Handle blade storage holds 3 blades
- Comfort grip for ease of use and slip protection
- Safety string cutter with recessed blade

Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
WK500V	037103209726	Quick-Change Comfort Grip Utility Knife with Blade Storage	5	25

Fixed Blade Knife



- DIY, professional and industrial uses
- Heavy-duty, fixed blade knife
- Uses all standard replacement utility blades
- Metal case painted red for easy visibility
- Knife comes with 3 blades

Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
WK9V	037103151377	Fixed Blade Utility Knife with 3 Blades-Carded	5	50

Heavy-duty Retractable Utility Knife

- DIY, professional and industrial uses
- Metal case painted red for easy visibility
- WK5V features zinc die-cast construction for added durability, non-slip handle for added safety, four blade positions for added versatility
- Uses standard utility knife blades
- Knife includes 3 blades



Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
WK5V	037103151544	Heavy-duty Retractable Utility Knife with 3 Blades-Carded	5	50

Retractable Utility Knife

- DIY, professional and industrial uses
- Popular all-purpose retractable knife
- Easy-run slide uses all standard replacement blades
- Metal case painted red for maximum visibility



Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
WK8V	037103151407	Retractable Utility Knife with 3 Blades-Carded	5	50

Snap Knife

- Suitable for all DIY uses
- Molded from high-impact plastic for long-term service
- WSK2V has metal-track to keep the blade secure in use



Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
WSK2V	037103151513	8 Point Snap Knife with Metal Track and 3 Blades-Carded	5	50

Utility Blades

- Wiss utility knife blades are high quality steel
- Replacement blades fit most utility knives
- Blades are available carded, and in dispensers
- Heavy-duty blades with sharp or hooked points



Cat. No.	UPC No.	Description	Shelf Pack	Case Qty.
RWK14D	037103151773	Heavy-duty .025" Blades, 100 per Dispenser	1	20
RWK14V	037103151445	Heavy-duty .025" Blades, 5 per card	10	100
RWK16V	037103151414	Heavy-duty .025" Hook Blades, 5 per Card	10	100

Shears and Scissors

As with other Wiss® products, the manufacture of shears and scissors begins with the finest quality cutlery steel. This combined with an extensive knowledge of metallurgy, the experience of skilled craftsmen, and the implementation of the quality control procedures have established Wiss® shears and scissors as the standard of excellence in the industry. Many progressive and innovative developments - Quick-Clip® Speed Cutters, Serrated Blade Shears - have helped to ensure that all Wiss® customers are provided with cutting tools that will cut easier, quicker, and better.

Stainless Steel Scissors and Shears

Introducing a new line of lightweight scissors and shears with heavy duty stainless steel blades for extra durability. This new line of lightweight Wiss® scissors features durable stainless steel blades and a selection of styles perfect for many different applications. All come in attractive retail packaging designed to appeal to specific consumer needs, from general home use to light commercial applications.

Home and Craft Scissors



- Soft comfort grips with oversize high-leverage bottom ring
- Stainless steel blades for corrosion resistance
- Serrated lower blade grips materials securely for more even cutting
- Adjustable pivot allows fine-tuning to most comfortable setting
- Straight blade can be easily re-sharpened
- Cuts paper, fabric, cardboard, craft materials, and more

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W812	037103211286	8 1/2	216	3 1/2		89	18	519	4

2 Piece Home, Craft, and Sew Scissor Set



- Set includes 5-inch and 8-inch scissors
- Soft comfort grips
- Stainless steel blades for corrosion resistance
- General-use design for all sewing, craft, and home applications

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
WHCS2	037103211316	5, 8 3/4	127, 222	3, 4 3/4		76, 121	32	898	4

Shop Shears

- High leverage comfort grip for right or left-handed use
- 420 Stainless blades provide maximum corrosion resistance
- Serrated lower blade grips materials for even cutting
- Adjustable pivot allows fine-tuning to comfortable setting
- Straight blade can be re-sharpened (professional re-sharpening is recommended for serrated blade)
- Blunt point on lower blade for added safety
- Notch on lower blade for faster, easier rope cutting
- Heavy-duty blade cuts cardboard, heavy fabric, rope, rubber, window screen, and more



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W912	037103211279	10	254	4 1/4		108	24	679	4

Take-Apart Utility Scissors

- Corrosion-resistant stainless steel blades separate for thorough cleaning
- Dishwasher-safe ergonomically designed polypropylene grips
- Serrated blades grip uneven materials for easier cutting
- Semi-circular notch on lower blade perfect for cutting plant stems and other similar-shaped items
- Cuts paper, fabric, cardboard, craft materials, and more



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W8TA	037103211293	8	203	4		100	16	499	4

Easy Snip Utility Shears

- Spring-loaded blades for reduced fatigue on repeated cuts
- Soft-touch co-molded handles for maximum comfort
- 420 Stainless blades provide maximum corrosion resistance
- Wire cutter notch for easy cutting of light-gauge wire or cable
- Safety-latch locks blades closed for storage
- Heavy-duty design is perfect for shop, garden, and craft jobs



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
WEZSNIP	037103211309	8 3/4	222	4		100	29	808	4

Solid Steel Trimmers



- Our finest solid steel shears
- Hot drop-forged from high carbon solid steel
- Hardened, ground, edged and adjusted to provide shears of outstanding cutting ability and durability . . . in the true Wiss® tradition
- Precision engineered to give longer cutting life and maximum cutting edge hardness and durability

Industrial Shears

INLAID



- Professional dressmaker and industrial use
- Forged from high carbon steel
- Black handle
- Hot drop-forged nickel-plated blades
- SET-EASY pivot

Cat. No.	UPC No.	Length		Inch	 mm	Pack Wt.		Shelf Pack
		Inch	mm			oz	g	
27N	037103580573	7	178	2 3/4	70	30	851	6
28N	037103580580	8	203	3 3/8	86	31	878	6
29N	037103580597	9	229	4	102	50	1418	6
426N*	037103223296	6 1/4	159	2 3/8	60	30	851	6
427N*	037103223333	8	203	3 3/8	86	31	878	6
428N*	037103223357	9	229	4	102	50	1418	6

*400 Series carded in vinyl pouch

Heavy Duty Industrial Shears

- Commonly used in cutting garments and industrial composite materials
- Forged from high carbon steel
- W20 and W22N have a black handle
- Hot drop-forged polished blades
- SET-EASY pivot
- W20P and W22P feature Red Cushion Grip handles for maximum comfort



W20P



W20

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W20	037103240132	10 3/8	264	4 3/4		121	94	2654	6
W22N	037103240200	12 1/2	318	5 5/8		143	126	3561	6
W20P	037103240149	10 3/8	264	4 3/4		121	98	2790	6
W22P	037103240217	12 1/2	318	5 5/8		143	126	3561	6

Heavy Duty Industrial Shears

Left Hand Model

- Forged from high carbon steel
- Black handle
- Hot drop-forged polished blades
- SET-EASY pivot



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W20LH	037103240187	10 3/8	264	4 3/4		121	94	2654	6

Upholstery, Carpet, Drapery, and Fabric Shears



- Forged from high carbon steel
- Thicker, heavy duty blades cut through multiple layers and tough material
- Hot drop-forged polished blades
- SET-EASY pivot

Cat. No.	UPC No.	Length		Inch	 mm	Pack Wt.		Shelf Pack
		Inch	mm			oz	g	
W20W	037103240194	10 3/8	264	4 3/4	121	98	2790	6
W22W	037103240231	12 1/2	318	5 5/8	143	130	3697	6

Carpet, Upholstery and Fabric Shears



- Forged from high carbon steel
- One blade ground to knife-edge for faster, cleaner, easier cutting of synthetic fibers
- Black handle
- Hot drop-forged polished blades
- SET-EASY pivot

Cat. No.	UPC No.	Length		Inch	 mm	Pack Wt.		Shelf Pack
		Inch	mm			oz	g	
W1225	037103240163	10 3/8	264	4 3/4	121	94	2654	6
W1226	037103240224	12 1/2	318	5 1/2	140	126	3561	6

High Leverage Industrial Shear



- Unique, high leverage handle design allows for cutting extra thick or tough upholstery, carpet and fabric
- Forged from high carbon steel
- One blade ground to knife-edge for faster, cleaner, easier cutting of tough synthetic fibers
- Red cushion grip handles provide maximum leverage
- Hot drop-forged polished blades, safely rounded for extra protection
- SET-EASY pivot

Cat. No.	UPC No.	Length		Inch	 mm	Pack Wt.		Shelf Pack
		Inch	mm			oz	g	
W1225HLSP	037103240170	10 3/8	264	4	102	98	2790	6

Double Rounded Shears

- Double rounded points for extra protection
- Forged from high carbon steel
- SET-EASY pivot



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W20SP	037103240156	10 3/8	264	4		102	94	2654	6

Industrial Straight Trimmers

- Industrial use
- Finest quality cutlery steel
- Black handle
- Hot drop-forged nickel-plated blades
- SET-EASY pivot



W30

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
37N	037103223302	7	178	2 7/8		73	28	794	6
T38N	037103223364	8 1/4	210	3 5/8		92	41	1163	6
W30	037103240248	10 3/8	264	4 1/2		114	94	2790	6
438N*	037103224200	8 1/4	210	3 5/8		92	46	1305	6

*400 Series carded in vinyl pouch

Belt and Leather Cutting Scissors

- One blade serrated and other is edged
- Black handle
- Forged from high carbon steel
- SET-EASY pivot



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
W8BLT	037103240255	8 1/2	222	3		76	84	2382	6

Pinking Shears



- Provides a superior, longer lasting cutting edge
- Bearing pivot reduces friction and finger fatigue which makes cutting easier
- Precision matched teeth provide a decorative ravel-resistant finish
- Forged from high carbon steel
- Black handle and nickel-plated blades

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
CB9	037103580405	9	225	3 5/8		92	66	1872	6
AA	037103580009	10 1/2	267	4		102	90	2552	6

Pocket Scissors



- Hot drop-forged solid steel
- Blades are a flat pattern with double blunt points
- Fully nickel-plated
- Ring handles

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
166	037103580795	6 1/4	158	2 3/4		70	16	459	6

Sewing and Embroidery Scissors



- Specially designed for intricate cutting, embroidery and fine needlework
- Hot drop-forged and nickel-plated
- Ring handle
- Double sharp points
- Flat pattern
- Attractive vinyl package

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
T764	037103581167	4 1/8	105	1 1/4		32	6	171	6
765	037103581174	5 1/8	130	2		51	11	312	6

Quick-Clip® Lightweight Speed Cutters



- Stainless steel replaceable blades
- Positive spring-action reopens blades for fast cutting
- Heavy duty contour design
- 1570B comes with sharp points, 1571B with blunt points
- Industrial PVC plastic handle

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
1570B	037103581266	4 3/4	121	1		26	10	284	6
1571B	037103581273	4 3/4	121	1		26	10	284	6
T9328	037103581808	Replacement blades for 1570B, packed 10 pair of blades and 40 blade screws.							10
T9329	037103581815	Replacement blades for 1571B blunt points, packed 10 pair of blades and 40 blade screws.							10

Industrial Thread Nippers



- Quality hot drop-forged cutlery steel
- Self-opening spring-action assures fast, effortless cutting
- Fully nickel-plated

TC5

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
TC1 Sharp points	037103580153	4 3/4	121	1 1/8		28	16	454	6
TC5 Blunt points	037103580276	4 5/8	117	1		26	16	454	6

Special Purpose Industrial Snips and Shears

Snips and shears designed for unique industrial applications requiring high quality Wiss® designed products to meet special needs.

Industrial Shears



- Used extensively in the poultry industry
- Forged from high carbon steel
- Nickel-plated blades and handle
- SET-EASY pivot
- New enlarged lower ring for added comfort

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
1DSN	037103223371	8 1/8	206	2 3/4		70	41	1163	6

Poultry Processing Shears



- Used extensively in poultry industry
- Made from carbon steel
- Special ball point for poultry processing
- Nickel-plated blades and handle
- Hot drop-forged commercial finish
- Adjustable nut

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
41DBN	037103223210	8	204	2 7/8		73	46	1304	6

High Leverage Shears



- Used extensively for wire cutting by florists
- Forged of high carbon steel
- Black handle
- Serrated nickel-plated blades for better grip of material

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
2DAN	03710322886	7 3/4	197	2		51	50	1418	6

Rug Shears for Hooked and Candlewick Rugs

- Hot drop-forged solid steel
- Offset black handle
- Nickel-plated blades with sharp points



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
RS1N	037103223319	8	203	2 7/8		73	41	1163	6

Kitchen Shears

- Hot drop-forged stainless steel
- Cut a wide variety of materials including twine, rope, cardboard, light metal, wire screens and cutting flowers
- Ideal for preparing food, cracking nuts, opening bottles, etc.
- One blade serrated
- Black baked enamel handles



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
KSRN	037103223500	8	203	2 5/8		67	96	1305	6

Industrial Trimming, Grape Thinning & Orchid Snips

- Hot drop-forged solid steel
- Straight, polished blades with adjustable nut
- Heavy pattern
- Coil spring handle opens blades after each cut
- Black handle with closing latch



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
C4ASN	037103223487	8	203	2 1/4		57	46	1305	6

Light Metal-Cutting Snips

- Used in electronic and appliance light metal cutting
- Comes with polished straight blades
- Black handle



Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
J7SN	037103223494	7	178	1		25	30	851	6

Electronics and Filament Scissors



- Hot drop-forged solid steel
- Coil spring handle opens blades after each cut
- Straight blades
- Polished blades with black handle

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
605	037103581112	5	127	3/4		19	21	596	6

Electrician's Scissors



- Hot drop-forged solid steel
- Scraper and file on back edge of blade
- Standard full blade run
- Fully nickel-plated for corrosion resistance
- Used for wire splicing, cutting insulation, stripping insulation and cutting harness ties

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
175E	037103580801	5 1/4	133	1 3/4		44	21	596	6

Electrician's Scissors



- Double stripping notch for 19 gauge (.035) and 23 gauge (.022) wire
- Hot drop-forged solid steel
- Scraper and file on back edge of blade
- Standard full drop run
- Fully nickel-plated

Cat. No.	UPC No.	Length		Inch		mm	Pack Wt.		Shelf Pack
		Inch	mm				oz	g	
175E5	037103580825	5 1/4	133	1 3/4		44	21	596	6
175E5V	037103582188	5 1/4	133	1 3/4		44	21	596	6

Note: 175E5V packaged in vinyl pouch.

Cat. No.	Page	Cat. No.	Page	Cat. No.	Page
W1225	266	M1RS1	248	WF18	257
W1225HLSP	266	M2R	248	WF24	257
W1226	266	M2RS1	248	WHN1	257
1570B	269	M300	251	WHCS2	262
1571B	269	M3R	248	WK500V	260
166	268	M400	251	WK5V	261
175E	272	M4R	250	WK8V	261
175E5	272	M5R	249	WK9V	260
175E5V	272	M6R	249	WKFQ4R	260
1DSN	270	M7R	249	WRPCLG	258
W20	265	M8R	250	WRPCMD	258
W20LH	265	M9R	250	WRPCSM	258
W20P	265	MPC3	250	WRPCWH1	258
W20SP	267	MPX	251	WRPCWH2	258
W20W	266	P406	249	WS3	255
W22N	265	P407	249	WS4	255
W22P	265	RS1N	271	WS6	255
W22W	266	RWK14D	261	WT1	257
27N	264	RWK14V	261	WSK2V	259
28N	264	RWK16V	261	WTNP1	259
29N	264	T38N	267	WSK2V	261
2DAN	270	T764	268	WSR1	259
W30	267	T9328	267		
37N	267	T9329	267		
41DBN	270	TC1	269		
426N	264	TC5	269		
427N	264	V10N	253		
428N	264	V19N	253		
438N	267	W12L	254		
605	272	W12LRB	254		
765	268	W14L	254		
W8BLT	267	W14LRB	254		
A10N	252	W5N	253		
A11N	252	W7BWN	254		
A12N	252	W7N	253		
A13N	252	W812	262		
A9N	252	W8TA	263		
AA	268	W912	263		
C4ASN	271	WC5L	256		
CB9	268	WC3S	256		
J7SN	271	WC5S	256		
KSRN	271	WEZSNIP	263		
M1R	248	WF12	257		