



# SANblade<sup>®</sup> QMC2462

## Dual Port 4-Gbps Fibre Channel (FC) Expansion Card for IBM<sup>®</sup> BladeCenter<sup>®</sup>

IBM Part Number: 26R0884

### High Performance

- 300,000 IOPS delivers high I/O transfer rates for storage applications
- Intelligent interleaved DMA (iiDMA) ensures maximum utilization of data links
- Out-of-order Frame Reassembly (OoOFR) reduces congestion and retransmissions

### Superior Scalability

- Multi-ID and N\_Port virtualization ready. Allows physical ports to be part of multiple logical networks
- Virtual fabric (VSAN) ready. Allows physical ports to be part of multiple logical networks
- Comprehensive Operating System (OS) driver support including Windows<sup>®</sup>, Linux<sup>™</sup>, Solaris<sup>™</sup>, NetWare<sup>®</sup>, VMware<sup>®</sup>, and AIX<sup>™</sup>

### Enhanced Reliability

- Overlapping protection domains for continuous protection of internal data paths
- Dual-port design protects against “single point of failure” via BladeCenter midplane routing to redundant switch modules



**QMC2462 Fibre Channel Expansion Card.** The QMC2462 enables 4-Gbps Fibre Channel in the IBM BladeCenter. The QMC2462 not only delivers unprecedented levels of performance and availability, but also provides intelligent networking features specific to enterprise class data centers.

**Enterprise Class Features.** The QMC2462 delivers unmatched performance by leveraging a single ASIC design, combining a unique hardware architecture to deliver over 300,000 IOPS, nearly 1.0 GBps throughput, and support for the PCI-X 133-MHz bus speed. More importantly, the QMC2462 HBA provides new intelligent storage networking features that redefine the enterprise class HBA, providing increased data protection, advanced frame routing, and enterprise wide management capabilities.

**Simplified Setup.** Point-and-click installation and configuration wizards simplify the HBA setup process. Storage administrators can quickly deploy HBAs across a SAN using QLogic SANSurfer HBA management tools and device utilities. The QMC2462 is also fully compliant with industry standard Application Programming Interfaces (APIs), including SNIA HBA API and SMI-S. This compatibility allows administrators to manage QLogic HBAs using third-party software applications.

**Comprehensive Operating System Support.** QMC2462 drivers exist for all major operating systems. A single driver strategy per OS allows storage administrators to easily deploy and manage HBAs in heterogeneous SAN configurations. In addition, QLogic's unique unified driver model, whereby firmware is bundled with the driver, eliminates any potential interoperability issues between the driver and firmware and reduces the number of software components to be managed. QLogic's comprehensive driver suite includes support for Intel, AMD, and Power PC based BladeCenter blades.

**Guaranteed Interoperability.** Storage partner certifications, combined with agency and regulatory testing, ensures all products meet world compliance hardware and software specifications. All our HBAs are tested extensively with third-party hardware, along with multiple software applications, to ensure best-in-class percent SAN interoperability and compatibility. You can be confident purchasing QLogic HBAs to meet your FC storage networking needs.

## Host Bus Interface Specifications

## Bus interface

- 64-bit, 133-MHz PCI-X

## Memory

- 1-MB SRAM per port
- 1-MB flash (SPI)
- 2-KB NVRAM (SPI)
- 4-KB EEPROM (I<sup>2</sup>C)

## Hardware platforms

- IBM HS20
- IBM HS40
- IBM LS20
- IBM LS21
- IBM LS41
- IBM JS20

## Compliance

- PCI-X Protocol Addendum to the PCI Local Bus Specification, revision 2.0a
- PCI Bus Power Management Interface Specification, revision 1.1

## Fibre Channel Specifications

## Data rate

- 4/2/1 Gbps auto-negotiation (4.25/2.125/1.0625 Gbps)

## Performance

- 150,000 IOPS per port

## Topology

- Point-to-point (N\_Port)
- Arbitrated loop (NL\_Port)
- Switched fabric (N\_Port)

## Logins

- Support for F\_Port and FL\_Port login
- 2,048 concurrent logins and 2,048 active exchanges per port

## Protocols

- FCP (SCSI-FCP)
- FC-TAPE (FCP-2)

## Compliance

- SCSI-3 Fibre Channel Protocol (SCSI-FCP)
- Fibre Channel Physical and Signaling Interface (FC-PH)
- Fibre Channel Physical and Signaling Interface 2nd Generation (FC-PH-2)
- Third Generation Fibre Channel Physical and Signaling Interface (FC-PH-3)
- Fibre Channel-Arbitrated Loop (FC-AL-2)
- Fibre Channel Fabric Loop Attachment Technical Report (FC-FLA)
- Fibre Channel-Private Loop Direct Attach Technical Report (FC-PLDA)
- Fibre Channel Tape (FC-TAPE) profile
- SCSI Fibre Channel Protocol-2 (FCP-2)
- Second Generation FC Generic Services (FC-GS-3)
- Third Generation FC Generic Services (FC-GS-3)
- Fibre Channel Framing and Signaling (FC-FS)

## Physical Specifications

## Ports

- Dual 4-Gbps FC

## Form factor

- IBM BladeCenter Expansion Card

## Environment and Equipment Specifications

## Airflow

- No airflow required

## Temperature

- Operating: 0°C/32°F to 55°C/131°F
- Storage: -40°C/-40°F to 70°C/158°F

## Humidity

- Relative (non-condensing): 5% to 95%
- Storage: 5% to 95%

## Power dissipation

- 6.7W (maximum)

## Tools and Utilities

## Management tools

- SANsurfer FC HBA Manager
- SANsurfer FC HBA Command Line Interface (CLI)

## Device utilities

- FLASUTIL for updating:
  - Firmware
  - Boot code
  - HBA parameters

## Boot support

- BIOS
- FCode

## APIs

- SNIA HBA API V2
- SMI-S
- FDMI

## Operating systems

- Windows
- Linux – Red Hat
- Linux – SuSE
- NetWare
- Solaris
- VMware
- AIX (IBM supplied driver)

## Ordering Information

- The QMC2462 is available from IBM (IBM part number: 26R0884)



Corporate Headquarters QLogic Corporation 26650 Aliso Viejo Parkway Aliso Viejo, CA 92656 949.389.6000

[www.qlogic.com](http://www.qlogic.com)

Europe Headquarters QLogic (UK) LTD. Surrey Technology Centre 40 Occam Road Guildford Surrey GU2 7YG UK +44 (0)1483 295825