




AD5020-7 SERIES



External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Bearing:Ball, Sleeve, Hypro bearing
Lead wire:UL1007AWG26
VOLTAGE AVAILABLE:12V,24V


Specifications(Nominal)

*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ○=1B1S ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Real Current (A)	Power (W)	Speed (rpm)	Maximum AirFlow		Maximum Pressure		*Noise Level (dB/A)	Weight (g)
50x50x20	AD5012LB-C71	◎ ※ ●	12	0.08	0.96	3600	0.340	12.00	0.080	2.00	24.0	31.0
	AD5012MB-C71	◎ ※ ●	12	0.10	1.20	4300	0.424	15.00	0.110	2.75	29.0	
	AD5012HB-C71	◎ ※ ●	12	0.13	1.56	5000	0.478	16.90	0.150	3.75	33.0	
	AD5012UB-C71	◎ ※ ●	12	0.19	2.22	6000	0.622	22.00	0.210	5.25	37.0	
	AD5024LB-C71	◎ ※ ●	24	0.06	1.44	3800	0.388	13.70	0.090	2.00	25.5	
	AD5024MB-C71	◎ ※ ●	24	0.08	1.92	4300	0.438	15.50	0.120	3.00	30.0	
	AD5024HB-C71	◎ ※ ●	24	0.11	2.64	5000	0.506	17.90	0.150	3.75	33.7	
	AD5024UB-C71	◎ ※ ●	24	0.15	3.60	6000	0.617	21.80	0.220	5.50	37.5	

Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓							

*Safety approvals

✓	✓		✓	✓