


FEATURES

- 375ps propagation delay
- 1.6V output swings
- Internal 75K Ω Input pull-down resistors
- ESD protection of 2000V

PIN CONFIGURATION/BLOCK DIAGRAM



SOIC
TOP VIEW

DESCRIPTION

The SY10EL89 is a differential fanout gate specifically designed to drive coaxial cables. The device is especially useful in Digital Video Broadcast applications. For this application, since the system is polarity-free, each output of the device can be used as an independent driver. The driver boasts a voltage gain of approximately 40 and produces output swings twice as large as a standard ECL output. When driving a coaxial cable, proper termination is required at both ends of the line to minimize signal loss. The 1.6V output swings allow for termination at both ends of the cable while maintaining the required 800mV swing at the receiving end of the cable. Because of the larger output swings, the device cannot be terminated into the standard $-2.0V$. All of the DC parameters are tested with a 50 Ω to $-3.0V$ load. The driver accepts a standard differential ECL input and can run off the Digital Video Broadcast standard $-5.0V$ supply.

PIN NAMES

Pin	Function
D	Data Inputs
Q0, Q1	Data Outputs

DC ELECTRICAL CHARACTERISTICS

VEE = VEE (Min.) to VEE (Max.); VCC = GND

Symbol	Parameter	-40°C			0°C			+25°C			+85°C			Unit
		Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	
IEE	Power Supply Current	18	23	28	18	23	28	18	23	28	18	23	28	mA
VOH	Output HIGH Voltage ⁽¹⁾	-1.23	-1.10	-0.98	-1.17	-1.05	-0.93	-1.13	-1.02	-0.90	-1.06	-0.96	-0.81	V
VOL	Output LOW Voltage ⁽¹⁾	-2.84	-2.72	-2.58	-2.84	-2.70	-2.56	-2.84	-2.70	-2.56	-2.84	-2.67	-2.51	V
VEE	Power Supply Voltage	-4.75	—	-5.5	-4.75	—	-5.5	-4.75	—	-5.5	-4.75	—	-5.5	V
I _{IH}	Input HIGH Current	—	—	150	—	—	150	—	—	150	—	—	150	μA

NOTE:

1 VOH and VOL specified for 50 Ω to $-3.0V$ load.

AC ELECTRICAL CHARACTERISTICS

VEE = VEE (Min.) to VEE (Max.); VCC = GND

Symbol	Parameter	-40°C			0°C			+25°C			+85°C			Unit
		Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	
tPLH tPHL	Propagation Delay to Output D	—	340	—	250	340	430	260	350	440	310	400	490	ps
tsKEW	Within-Device Skew	—	5	20	—	5	20	—	5	20	—	5	20	ps
VPP	Minimum Input Swing ⁽¹⁾	150	—	—	150	—	—	150	—	—	150	—	—	mV
VCMR	Common Mode Range ⁽²⁾	-0.4	—	(2)	-0.4	—	(2)	-0.4	—	(2)	-0.4	—	(2)	V
tr tf	Output Rise/Fall Times Q (20% to 80%)	—	330	—	205	330	455	205	330	455	205	330	455	ps

NOTES:

1. Minimum input swing for which AC parameters are guaranteed. The device has a DC gain of ≈ 40 .
2. The CMR range is referenced to the most positive side of the differential input signal. Normal operation is obtained if the HIGH level falls within the specified range and the peak-to-peak voltage lies between V_{ppmin} and 1V. The lower end of the CMR range is dependent on VEE and is equal to $VEE + 3.0V$.




Figure 1. Termination Configuration

PRODUCT ORDERING CODE

Ordering Code	Package Type	Operating Range
SY10EL89ZC	Z8-1	Commercial
SY100EL89ZC	Z8-1	Commercial