

1 | 2 3 | 4 | 5 | 6 |

10086534-X MM DD Y Y LF

LEAD FREE

OVERALL LENGTH IN CENTIMETER

OVERALL LENGTH IN METER
EXAMPLE OF MM DD: 1.5M CABLE= 0150
5M CABLE= 0500

SIGNAL WIRE GAGE
N: 26 AWG

NOTES:

1. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
2. PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE.
3. LABEL INFORMATION:
FCI
FCI PART NO.
DATE CODE
COUNTRY ORIGIN
4. TOLERANCES:
0-1 = $\pm 15\text{mm}$
1-10 = $\pm 2\%$
<10 = $\pm 4\%$

A


A

B

B

WIRING DIAGRAM

POS P1-P2	COLOR CODE	TWISTED PAIR
B1	BLUE	1
A2	WHITE	
B2	ORANGE	2
A1	WHITE	
B3	GREEN	3
A4	WHITE	
B4	BROWN	4
A3	WHITE	
B5	BLUE	5
A6	RED	
B6	ORANGE	6
A5	RED	
B7	GREEN	7
A8	RED	
B8	BROWN	8
A7	RED	
B9	BLUE	9
A10	BLACK	
B10	ORANGE	10
A9	BLACK	
B11	GREEN	11
A12	BLACK	
B12	BROWN	12
A11	BLACK	



mat'l. code				surface		tolerance		projection	product family
ltr	ecn no	dr	date	ISO 1302		ISO 406	ISO 1101		
A	M08-0039	AGS	02/12/08	tolerances unless otherwise specified				METER	
B	M08-0105	AGS	04/11/08	angles	linear	SEE TABLE		scale NTS	
						dr	A. GARCIA	02/12/08	
						engr	J. DUARTE	02/12/08	
						chr	J. DUARTE	02/12/08	
						appd	J. DUARTE	02/12/08	
sheet		revision	B						
index		sheet	1						

dwg no sheet 1 of 1 size
10086534 A3
type Product Customer Drawing

form: A3

1

2

3

4

5

6

PDM: Rev:B

STATUS:Released

Printed: Jan 19, 2011

FCI
FCIconnection.com

Copyright FCI

