






AMPLIVAR Ring Tongue Terminals

A
 Insulation Support

B
 Oval Hole

C
 Non-Insulation Support

D
 Heavy Duty Oval Hole

E
 Anti-Rotational

Type	Wire Range		Insul. Size	Hole Dia.	Stud Size/ Dia.	Stock Thk.	Material and Finish	Dimensions				Part Number
	AWG	mm ²						W	L	E	C	
A	29-22	0.284-0.643	.040-.060 1.02-1.52	.197 5.00	10	.020 0.51	Tin Plated Brass	.342 8.69	.833 21.16	.662 16.81	.312 7.92	63399-1
			.100-.140 2.54-3.56	.171 4.34	8	.020 0.51	Tin Plated Brass	.342 8.69	.833 21.16	.662 16.81	.312 7.92	60321-2
A	23-19	0.574-0.912	.125-.165 3.18-4.19	.171 4.34	8	.020 0.51	Tin Plated Brass	.300 7.62	.700 17.73	.550 13.97	.230 5.84	60323-2
			.100-.140 2.54-3.56	.197 5.00	10	.020 0.51	Tin Plated Brass	.342 8.69	.833 21.16	.662 16.81	.312 7.92	60319-2
A	22-18	0.643-1.024	.125-.165 3.18-4.19	.265 6.73	1/4"	.025 0.64	Tin Plated Brass	.420 10.67	.872 22.15	.662 16.81	.312 7.92	63612-1
					6	.025 0.64	Tin Plated Brass	.290 7.37	.500 12.70	.355 9.02	.195 4.95	63649-1
C	22-18	0.643-1.024	—	—	8	.025 0.64	Brass	.290 7.37	.500 12.70	.355 9.02	.195 4.95	63446-1
					8	.025 0.64	Tin Plated Brass	.290 7.37	.500 12.70	.355 9.02	.195 4.95	63446-2
					1/4"	.025 0.64	Tin Plated Brass	.420 10.67	.702 17.83	.492 12.50	.312 7.92	62835-1
A	20-16	0.183-1.29	.125-.165 3.18-4.19	.171 4.34	8	.020 0.51	Tin Plated Brass	.300 7.62	.695 17.65	.545 13.84	.230 5.84	60322-2
A	18-14	1.024-1.628	.100-.140 2.54-3.56	.171 4.34	8	.020 0.51	Brass	.342 8.69	.833 21.16	.662 16.81	.312 7.92	60320-1
							Tin Plated Brass	.342 8.69	.833 21.16	.662 16.81	.312 7.92	60320-2
E	18-14	1.024-1.628	.173 4.39	.171 4.34	8	.028 0.71	Lu-Bronze	.370 9.40	.915 23.24	.730 18.54	.380 9.65	485079-1 ¹
			.080-.120 2.03-3.05	.185 4.70	8	.028 0.71	Lu-Bronze	.365 9.27	.882 22.40	.700 17.78	.380 9.65	485044-1 ¹
D	14-12	1.628-2.05	—	.180 4.57	8	.025 0.64	Brass	.342 8.69	.833 21.16	.657 16.69	.312 7.92	62755-1
A	13-11	1.83-2.3	.085-.150 2.16-3.81	.180 4.57	8	.025 0.64	Brass	.342 8.69	.833 21.16	.657 16.69	.312 7.92	61710-1
				.180 4.57	8	.025 0.64	Tin Plated Brass	.342 8.69	.665 16.89	.495 12.57	.312 7.92	350571-1
C	13-11	1.83-2.3	—	.197 5.00	10	.025 0.64	Tin Plated Brass	.342 8.69	.665 16.89	.495 12.57	.312 7.92	640212-1
							Tin Plated Brass	.342 8.69	.665 16.89	.495 12.57	.312 7.92	60752-2
A	(2) 17 (2) 15 or	1.15 or 1.45 or	.150-.190 3.68-4.83	.171 4.34	8	.025 0.64	Tin Plated Brass	.342 8.69	.827 21.01	.656 16.66	.312 7.92	60752-2
B	17-13 1/2	1.51-1.78	—	.180 4.57	8	.020 0.51	Brass	.310 7.87	.692 17.58	.492 12.50	.312 7.92	63147-1

¹High conductivity copper-tin-zinc alloy.

Note: The part numbers listed are for use with existing machine models. For AMP-O-LECTRIC Model G applicators part numbers, call the Technical Support Center at 1-800-522-6752.