

S15SC4M

40V 15A


FEATURES

- Tj150°C
- P_{RRSM} avalanche guaranteed
- Small θ_{jc}
- High current capacity

APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified T_c=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-40~150	°C
Operating Junction Temperature	T _j		150	°C
Maximum Reverse Voltage	V _{RM}		40	V
Repetitive Peak Surge Reverse Voltage	V _{RRSM}	Pulse width 0.5ms, duty 1/40	45	V
Average Rectified Forward Current	I _O	50Hz sine wave, R-load, Rating for each diode I _O /2, T _c =135°C	15	A
Peak Surge Forward Current	I _{FSM}	50Hz sine wave, Non-repetitive 1 cycle peak value, T _j =125°C	170	A
Repetitive Peak Surge Reverse Power	P _{RRSM}	Pulse width 10 μs, Rating of per diode, T _j =25°C	330	W
Mounting Torque	TOR	(Recommended torque: 0.5N·m)	0.8	N·m

● Electrical Characteristics (If not specified T_c=25°C)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	V _F	I _F =7.5A, Pulse measurement, Rating of per diode	Max.0.55	V
Reverse Current	I _R	V _R =V _{RM} , Pulse measurement, Rating of per diode	Max.5	mA
Junction Capacitance	C _j	f=1MHz, V _R =10V Rating of per diode	Typ.340	pF
Thermal Resistance	θ_{jc}	junction to case	Max.1.2	°C/W

S15SC4M

Forward Voltage




S15SC4M Junction Capacitance




S15SC4M


Reverse Current




S15SC4M Reverse Power Dissipation




$T_j = 150^\circ\text{C}$



S15SC4M Forward Power Dissipation




$T_J = 150^\circ\text{C}$




S15SC4M


Derating Curve



$V_R = 20V$



S15SC4M Peak Surge Forward Capability



SBD Repetitive Surge Reverse Power Derating Curve

