


NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:
 - 1.1 BODY & PANEL NUT: NICKEL PLATED BRASS
 - 1.2 CENTER CONTACT AND INTERMEDIATE CONTACT: GOLD PLATED BERYLLIUM COPPER
 - 1.3 DIELECTRIC: PTFE (TEFLON)
 - 1.4 GASKET: SILICON RUBBER
 - 1.5 GROUND LUG & LOCKWASHER: NICKEL PLATED COPPER ALLOY
2. ELECTRICAL
 - 2.1 FREQUENCY (MAX): 500 MHz
 - 2.2 IMPEDENCE: NON-CONSTANT
3. PANEL NUT TORQUE (MAX): 35 INCH POUNDS
4. PANEL THICKNESS (MAX): .250



**RECOMMENDED
PANEL CUTOUT**

<p>EMERSON Network Power Connectivity Solutions</p> <p><small>This PROPRIETARY Document is property of Emerson Network Power, Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not tracked or copied without permission and is retrievable upon demand.</small></p> <p><small>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.</small></p>	<p>3RD ANGLE PROJECTION</p>	<p>Trompeter</p>	
	<p>RoHS <input checked="" type="checkbox"/></p> <p>2002/95/EC</p>	<p>Title: TRS BULKHEAD SOLDER POT JACK</p>	
<p>UNLESS OTHERWISE SPECIFIED UNITS: INCH</p> <p>.XX ±.02 .XXX ±.005 ANGLES ±2°</p>		<p>Model No. BJ150FL</p>	
<p>Size A</p>	<p>DO NOT SCALE DRAWING</p>	<p>Date: 5/9/2014</p>	<p>Sheet 1 of 1</p>