


MICRO SWITCH
a Honeywell Division

SWITCH-BASIC

FED. MFG. CODE 91 929

CATALOG LISTING
BZ-2RQ1008-A2
PAGE 1 OF 1
ISSUE **M**
6

REPLACES X97331-BZ
RELEASE NO. PR-20635
CHECK
REVISIONS
A CO-76742 LJJ 2 MAR 94
B CO-77589 LJJ 31 MAR 94
C CO-77853 MAM 17 AUG 94
D C082133 J A K 30 JUL 96
E C093346 D L T 12 AUG 98
CHECK
J W B 20 AUG 93
J W B 18 AUG 93
CHECK
D D M / C A D
DRAWN
L J J




3X 6-32 UNC X (.218)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER

NOTE
 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS
 2 HARDWARE FURNISHED UNASSEMBLED

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 5 OZ MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ±	
RELEASE FORCE ----- 2 1/2 OZ MIN	L9 10A 125, <u>250</u> OR 480 VAC 1/2A 125 VDC, 1/4A 250 VDC		
DIFFERENTIAL TRAVEL ---- .0004-.002	L288		
OVERTRAVEL ----- .219 MIN	CE		
OVERTRAVEL FORCE ----- 10 OZ MAX			
		WEIGHT .094 LB	