





△E

-
- Technical drawing of a mechanical part, likely a bracket or support structure, showing a dimension of 13.74 with a tolerance of ± 0.1 (indicated as [349.1]). The drawing includes a cross-section view of the part, showing internal features and a central slot.



CAD_FILENAME/LAYERS

 A C

FROV45SC12.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBERRUNNER 12x4 OUTSIDE VERTICAL
45° ANGLE SPLIT COVER (FROV45SC12)
CUSTOMER DRAWING

(.X)	±	(.XXX)	±
(.XX)	±.03	(.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

MAT'L:	
--------	--

MAT'L: ABS

DRAWING NO.
37617-83

DWG
A
SIZE

-	-----	---	---	E. REVISED PART WEIGHT	-----	--	--		
-	-----	---	---	D. REVISED GENERAL NOTES C. REVISED CAD FILENAME	-----	--	--		
1	7-7-06	DTP	RN	B. REVISED DRAWING TITLE A. REVISED AND REDRAWN	37617-83	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMB