



EP10 LM259X Inductor
150 uHy



ELECTRICAL SPECS:

- 1: INDUCTANCE: @ 10 kHz, 0.1 Vrms
(1 thru 4 to 5 thru 8) = 150 - 195 uHy
- 2: DCRs:
(1 thru 4 to 5 thru 8) = 0.180 Ohms Max.
- 3: SRF: 950 kHz Min
- 4: HIPOT: 500 VDC
Winding to core (2 Sec., 5 mA Max)



All pins may not be used.
Specifications at room temperature of 25 C.

A	2/28/03		KAM	Production Release			
REV.	DATE	ECN	BY	DESCRIPTION			
TOLERANCES ON				Newava Tech. Watertown, SD 57201 605-886-0264		150 uHy Inductor	
.XXX		.XX	ANGLE				
+ -		+ -	+ -				
			DATE				
DRAWN:				SCALE	MODEL	DRAWING NO.	
CHECKED: -				-			
APPROVED: -				- KAM	NEXT ASSY:	S34547	
THIS PRINT MUST NOT BE COPIED IN WHOLE OR IN PART						OR USED DETRIMENTALLY TO OUR INTEREST	
						SHEET 1 OF 1	