




+ WIRE AND CABLE

HOOK UP WIRE



✓ Active

TE CONNECTIVITY (TE)

55A0811-10-2-1KF

Raychem | RC , SP

55A0811-10-2-1KF

TE Internal Number: CA0128-000

Alias ID: 8-1899093-2

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 55

Voltage Rating (V) 600

Insulation Material Radiation-Crosslinked, Modified ETFE

Conductor Material Tin-Plated Copper

Wire Size (AWG) 10

PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

Wire, Radiation-Crosslinked, Modified ETFE-Insulated, Normal Weight, General Purpose, 600 Volt

PDF

English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Extruded, Modified, Fluoropolymer-Insulated Copper Or Copper Alloy

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 55

Cable Style Primary

Product Classification Cable - High Performance - Spec 44, 55 & RCW

Product Type Wire

Configuration Features

Number of Strands 37

Number of Conductors 1

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Insulation Material Radiation-Crosslinked, Modified ETFE

Conductor Material Tin-Plated Copper

Wire Color Red

Dimensions

Strand Size (AWG) 26

Wire Size (AWG) 10

Wire Size (mm²) 5.26

Conductor Diameter 2.79 mm [.11 in]

Overall Outside Diameter 3.4 mm [.134 in]

Insulation Thickness (in) .009

Wire Diameter 3.403 mm [.134 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 200

Other

Comment 1000 ft per spool ± 0 ft

Wire Source United States

PRODUCT COMPLIANCE



Statement of Compliance

[Statement of Compliance](#)

PDF

