


FT

- Terminal Pins : Kinked
- Actuator Color : Yellow

Washable

Ultra-Miniature Toggle Switch

RoHS Compliant




Features

1. Ultra-miniature toggle switch for high density mounting.
2. Washable.
3. Terminal pin pitch : 2.54 mm.
4. Independent detent mechanism ensures light operational feel.
5. Clip contact mechanism for long-term contact reliability.
6. Gold-plated contacts.

Specifications

Rating	Max.	28VDC 0.4VA max.
	Min.	1μ A 20mVDC
Initial contact resistance	100mΩ max. (1.5mA 200μ VAC)	
Dielectric strength	250VAC 1 minute	
Insulation resistance	500MΩ min. (250VDC)	
Electrical life	10,000 cycles at max. rating	
	50,000 cycles at min. rating (D,E type)	
	30,000 cycles at min. rating (F,G,H type)	
Operating temperature range	-40°C~+85°C	
Storage temperature range	-40°C~+85°C	

Part Numbering



Terminal style of [2] (Style : PC Terminal)	Terminal style of [4] (Style : V/M Terminal)	Terminal style of [5] (Style : R/A Terminal)


(ON) : Momentary.

SPDT

PC Straight



Terminal numbers are not shown on the switch.




Switching function			
Part No.			
FT1D-2M-Z	ON	—	ON
☆ FT1E-2M-Z	ON	OFF	ON
☆ FT1F-2M-Z	ON	—	(ON)
★ FT1G-2M-Z	(ON)	OFF	(ON)
▲ FT1H-2M-Z	ON	OFF	(ON)
Connecting terminals	2—3	—	2—1

DPDT

PC Straight



Terminal numbers are not shown on the switch.




Switching function			
Part No.			
FT2D-2M-Z	ON	—	ON
☆ FT2E-2M-Z	ON	OFF	ON
★ FT2F-2M-Z	ON	—	(ON)
★ FT2G-2M-Z	(ON)	OFF	(ON)
★ FT2H-2M-Z	ON	OFF	(ON)
Connecting terminals	2—3 5—6	—	2—1 5—4

SPDT

Right Angle Terminal



Terminal numbers are not shown on the switch.




Switching function			
Part No.			
FT1D-5M-Z	ON	—	ON
FT1E-5M-Z	ON	OFF	ON
☆ FT1F-5M-Z	(ON)	—	ON
★ FT1FA-5M-Z	ON	—	(ON)
☆ FT1G-5M-Z	(ON)	OFF	(ON)
★ FT1H-5M-Z	(ON)	OFF	ON
▲ FT1HA-5M-Z	ON	OFF	(ON)
Connecting terminals	2—1	—	2—3

DPDT

Right Angle Terminal



Terminal numbers are not shown on the switch.







Switching function			
Part No.			
☆ FT2D-5M-Z	ON	—	ON
★ FT2E-5M-Z	ON	OFF	ON
★ FT2F-5M-Z	(ON)	—	ON
▲ FT2FA-5M-Z	ON	—	(ON)
▲ FT2G-5M-Z	(ON)	OFF	(ON)
▲ FT2H-5M-Z	(ON)	OFF	ON
▲ FT2HA-5M-Z	ON	OFF	(ON)
Connecting terminals	2—1 5—4	—	2—3 5—6

FT

SPDT


Vertical mounting terminal






Switching function			
Part No.			
☆FT1D-4M-Z	ON	—	ON
★FT1E-4M-Z	ON	OFF	ON
★FT1F-4M-Z	ON	—	(ON)
▲FT1FA-4M-Z	(ON)	—	ON
▲FT1G-4M-Z	(ON)	OFF	(ON)
▲FT1H-4M-Z	ON	OFF	(ON)
▲FT1HA-4M-Z	(ON)	OFF	ON
Connecting terminals	2—3	—	2—1

DPDT

Vertical mounting terminal



Switching function			
Part No.			
FT2D-4M-Z	ON	—	ON
★FT2E-4M-Z	ON	OFF	ON
★FT2F-4M-Z	ON	—	(ON)
▲FT2FA-4M-Z	(ON)	—	ON
▲FT2G-4M-Z	(ON)	OFF	(ON)
▲FT2H-4M-Z	ON	OFF	(ON)
▲FT2HA-4M-Z	(ON)	OFF	ON
Connecting terminals	2—3 5—6	—	2—1 5—4

Soldering Specifications


(1) Manual Soldering

Device : Soldering iron
380°C, Max.; 3 seconds, Max.

(2) Auto Soldering

Device : Jet wave type or dip type
275°C, Max.; 6 seconds, Max.

- Pre-heating should be done at temperatures from 80 to 120°C and within 120 sec.



- When soldering two or more terminals to a common land, use solder resist to separate them.

Flux Cleaning

- Solvent : Fluorine or Alcohol type.
- Cleaning after soldering should be done after the PC board is exposed to room temperature (30°C or below) for 1 to 2 hours.
- Do not use ultrasonic cleaning.

Packaging Specifications

Plastick Pack

