

PART NUMBER	LED COLOR
591-2001-002	HI.EFF. RED
591-2001-007	
591-2001-013	
591-2101-002	AlGaAs RED
591-2101-007	
591-2101-013	
591-2201-002	HI.INTENSITY GREEN
591-2201-007	
591-2201-013	
591-2301-002	GREEN
591-2301-007	
591-2301-013	
591-2401-002	YELLOW
591-2401-007	
591-2401-013	
591-2601-002	BLUE
591-2601-007	
591-2601-013	
591-2701-002	AlInGaP YELLOW
591-2701-007	
591-2701-013	

LED COLOR = HI.EFF. / RED - GREEN - YELLOW						
OPERATING CHARACTERISTICS AT 25°C AMBIENT						
CHARACTERISTICS		MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	RED	5.6	9.8	14.0	mcd	I f = 10 mA
	GREEN	7.1	10.6	14.0		
	YELLOW	7.1	12.6	18.0		
FORWARD VOLTAGE	RED	2.0	2.5		V	I f = 10 mA
	GREEN		2.0	2.5		
	YELLOW		2.0	2.5		
REVERSE VOLTAGE	RED		5		V	I r = 10 µA
	GREEN		5			
	YELLOW		5			
PEAK WAVELENGTH	RED		635		nm	I f = 10 mA
	GREEN		572			
	YELLOW		586			
DOMINANT WAVELENGTH	RED	622	628	634	nm	I f = 10 mA
	GREEN	564	570	576		
	YELLOW	580	587	595		

LED COLOR = HI.EFF. / RED - GREEN - YELLOW			
ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT			UNITS
POWER DISSIPATION	RED	95	mW
	GREEN	95	
	YELLOW	95	
	RED	30	
CONTINUOUS FORWARD CURRENT	GREEN	30	mA
	YELLOW	30	
	RED	30	
	YELLOW	30	
OPERATING TEMPERATURE	R-G-Y	-40 TO 100	°C
STORAGE TEMPERATURE	R-G-Y	-40 TO 100	°C

LED COLOR = RED (AlGaAs) GREEN (HI.INT.) YELLOW (AlInGaP)						
OPERATING CHARACTERISTICS AT 25°C AMBIENT						
CHARACTERISTICS		MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY	AlGaAs RED		23.9		mcd	I f = 10 mA
	HI.INT. GREEN		9.1			
	AlInGaP YELLOW		33.6			
FORWARD VOLTAGE	AlGaAs RED		1.8	2.4	V	I f = 20 mA
	HI.INT. GREEN		2.1	2.6		
	AlInGaP YELLOW		2.0	2.4		
REVERSE VOLTAGE	AlGaAs RED		5		V	I f = 10 mA
	HI.INT. GREEN		5			
	AlInGaP YELLOW		5			
DOMINANT WAVELENGTH	AlGaAs RED		638		nm	
	HI.INT. GREEN		569			
	AlInGaP YELLOW		595			


LED COLOR = RED (AlGaAs) GREEN (HI.INT.) YELLOW (AlInGaP)			
ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT			UNITS
POWER DISSIPATION	R-G-Y	100	mW
DERATE LINEARLY FROM 25°C	AlGaAs RED	0.8	mA/°C
	HI.INT. GREEN	0.6	
	AlInGaP YELLOW	0.6	
	AlGaAs RED	40	
CONTINUOUS FORWARD CURRENT	HI.INT. GREEN	30	mA
	AlInGaP YELLOW	50	
	AlGaAs RED	200	
	HI.INT. GREEN	120	
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1 ms PULSE WIDTH)	AlInGaP YELLOW	160	mA
	AlInGaP YELLOW	160	
OPERATING TEMPERATURE	R-G-Y	-55 TO 100	°C
STORAGE TEMPERATURE	R-G-Y	-55 TO 100	°C
INFRARED REFLOW SOLDERING	R-G-Y	260°C FOR 5 SEC	
VAPOR PHASE SOLDERING	R-G-Y	215°C FOR 3 MIN	

LED COLOR = BLUE					
OPERATING CHARACTERISTICS AT 25°C AMBIENT					
CHARACTERISTICS	MIN	TYP	MAX	UNITS	TEST CONDITIONS
LUMINOUS INTENSITY		6.0		mcd	I f = 10 mA
FORWARD VOLTAGE		3.5	4.2	V	I f = 10 mA
REVERSE CURRENT		0.01	10	µA	V r = 5 V





LED COLOR = BLUE		
ABSOLUTE MAXIMUM RATING AT 25°C AMBIENT		UNITS
POWER DISSIPATION	100	mW
DERATE LINEARLY FROM 55°C	0.44	mW/°C
CONTINUOUS FORWARD CURRENT	20	mA
OPERATING TEMPERATURE	-40 TO 100	°C
STORAGE TEMPERATURE	-40 TO 100	°C
SOLDER PROFILE: 1R 235°C PEAK FOR 15 sec / 185°C FOR 90 sec MAX		




TAPING SPECIFICATION



TOLERANCE: .004 UNLESS OTHERWISE SPECIFIED
MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY



13 INCH DIA. REEL SPECIFICATIONS



7 INCH DIA. REEL SPECIFICATIONS

- NOTES :
- 1- MILLIMETER DIMENSIONS SHOWN FOR REFERENCE ONLY
 - 2- PAD NUMBERS ARE FOR REFERENCE ONLY, DESIGNATION NON-EXISTENT ON PART
 - 3- STORAGE CONDITIONS FOR TAPED PRODUCT: RE-TAPING MAY BE NECESSARY FOR PRODUCTS STORED MORE THAN TWELVE MONTHS
 - 4- ORDER QUANTITY IS LED ASSEMBLIES, NOT REELS
 - 5- ...-002 SUFFIX MEANS PARTS ARE PACKED ON A 20 pc SAMPLE STRIP
...-007 SUFFIX MEANS PARTS ARE PACKED ON A 7 INCH REEL, 400 pcs/REEL
...-013 SUFFIX MEANS PARTS ARE PACKED ON A 13 INCH REEL, 1600 pcs/REEL
 - 6- LENS MOVEMENT IN RELATIONSHIP TO THE HOUSING IS:
.009" T.I.R. VERTICALLY
.007" T.I.R. HORIZONTALLY
 - 7- FRONT AND REAR TERMINALS OF THE ASSEMBLY TO BE WITHIN .005 COPLANARITY
 - 8- LED LEAD FRAME MATERIAL:
CORE MATERIAL = COPPER
1st PLATING = Ag-100%, THICKNESS ABOUT 90 MICRO-INCH
2nd PLATING = 90% Sn - 10% Pb, THICKNESS RANGE 200 to 800 MICRO-INCH
 - 9- DIALIGHT PART NUMBERS =
591-2x01-002, 591-2x01-007, 591-2x01-013
 10. DEVICE HAS A MOISTURE SENSITIVITY LEVEL "2" CAUTION
LABEL APPLIED AS PER JEDEC STD. 033

REV.	ECN NO.	REVISIONS	DRN.	CKD.	APP.	DATE
A	---	---	---	---	---	---
B	---	---	---	---	---	---
C	---	---	---	---	---	---
D	---	REDRAWN WITH CHANGES -NEW HSG AND LENS DESIGN -ADDED NOTE 6-8 -CHANGE LED CHARACTERISTC	YY	---	NO	3-7-94
E	---	ADDED HI. GREEN AND AlInGaP YELLOW AND CHANGE TO ANOTHER AlGaAs RED CHANGE NOTE 8	AV	DC	NO	3-8-00
F	---	ADD ...2601... (BLUE) CORRECT HI.EFF. LED SPEC	AV	DC	NO	10-10-00
G	---	ADDED NOTE 10	YIS	JMC	NO	2-14-03
H	---	UPDATED LED SPEC. FOR HI.EFF. RED, GREEN & YELLOW	YIS			