

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5018643091

Status:


Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.50mm Pitch Easy-On FFC/FPC-to-Board Connector, Receptacle Housing Assembly, Right-Angle, Surface Mount, with Grounding Terminals, Gold (Au) Plating, 30 Circuits



Documents:	
3D Model	Product Specification PS-501864-004-001 (PDF)
3D Model (PDF)	Packaging Specification 5018649200-SPK-200 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	501864
Comments	Requires a custom FFC/FPC with notches
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	822350663427
Physical	
Actuator Type	FFC/FPC-to-Board
Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Contact Position	Bottom
Durability (mating cycles max)	20
Flammability	94V-0
Mated Height	4.85mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	741.465/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.100µm
Plating min - Termination	0.051µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	50V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	5018649200-SPK-200

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

501864 Series

Mates With

Premo-Flex LVDS Cable [15022](#)

Use With

Plug Jacket [5017833009](#) . Plug Jacket Cover [5017843008](#)

This document was generated on 07/28/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION