


DRAWING MADE IN AMERICAN PROJECTION

REVISIONS



LTR	DESCRIPTION	DATE	DWN	APVD
E1	REVISED PER ECO-09-022178	25SEP09	KK	AEQ

NUMBER C-160826



NOTES:

- 1 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED).
- 2 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED) AMPOMATOR APPLICATION
- 3 GENERAL TOLERANCE ± 0.3 (.012)
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



0.5(.020) MAX. CUT OFF

CUSTOMER COPY FOR REFERENCE ONLY

©1981 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

AMP-ESPAÑOLA
BARCELONA

WIRE-RANGE 22-18 AWG .045-.100 DIA.
0.30-0.81 mm 1.1-2.5 mm DIA.

FIRST USED

SCALE
N.D.S.SIZE
A

NO

C-160826

REV
E1

NAME

POSITIVE LOCK RECEPTACLE

6-160826-8	PH. BRONZE	PRE-TIN PLATED
6-160826-7	BRASS	PRE-TIN PLATED
160826-4	PH. BRONZE	TIN PLATED
160826-3	BRASS	TIN PLATED
160826-2	PH. BRONZE	—
160826-1	BRASS	—

ORDER NO.	MATERIAL	PLATING
-----------	----------	---------

DR	DATE	DE	DATE
----	------	----	------

CHK	DATE	APP	DATE
-----	------	-----	------