


SPECIFICATION CONTROL DRAWING



Product Revision		Product Dimensions			Cable Dimensions			
Product Name		L max	ØA min	ØB min	ØD max	ØE min	ØG max	J±1.3 (J±0.05)
D-107-00	K	20.4 (0.805)	5.95 (0.235)	6.45 (0.255)	6.45 (0.255)	3.20 (0.125)	5.95 (0.235)	7 (0.275)


MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
2. SOLDER PREFORM WITH FLUX:
SOLDER: TYPE Sn63 per ANSI-J-STD-006.
FLUX: TYPE ROL1 per ANSI-J-STD-004.
THERMAL INDICATOR: Violet.
3. MELTABLE RINGS: Thermally stabilized thermoplastic. Color: gray.

APPLICATION

1. This part is designed to provide an environment protected shield termination on cables, rated for 125°C minimum, meeting the dimensional criteria listed, having tin or silver plated copper shields.
2. Install using Raychem-approved convection or infrared tools in accordance with Raychem assembly procedure RCPS-100-70.
3. Assemblies will meet requirements of Raychem specification RT-1404 and National Aerospace Standard NAS-1747.
4. Temperature range: -55°C to +150°C.

For best results, prepare the cable as shown:



* A trademark of Raychem Corporation.

Raychem		THERMOFIT DEVICES		Raychem Corporation 300 Constitution Drive Menlo Park, CA 94025 USA		TITLE: SOLDERSLEEVE* SHIELD TERMINATOR			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.						DOCUMENT NO.: D-107-00			
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A		ANGLES: N/A ROUGHNESS IN MICRON		Raychem reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		DCR NUMBER: D981829		REPLACES: D961391	
DRAWN BY: M. FORONDA		DATE: 28-Oct-98		PROD. REV. SEE TABLE		DOC ISSUE: 3	SCALE: None	SIZE: A	SHEET: 1 of 1

If this document is printed it becomes uncontrolled. Check for the latest revision