



LEDTECH ELECTRONICS CORP.

U.S. Sales Office  
9029 Owensmouth Avenue  
Canoga Park, CA 91304  
Phone: (818) 701-7240  
Fax: (818) 701-7217

# SPECIFICATION

*PART NO. : UT1893-45-0125*


**5.0mm ROUND PHOTOTRANSISTOR**



| Approved by | Checked by  | Prepared by  |
|-------------|-------------|--------------|
| <i>Tung</i> | <i>Andy</i> | <i>Haibo</i> |

## Description

The UT1893-45-0125 is a high speed and high sensitive silicon NPN epitaxial planar phototransistor in a standard 5.0mm package. The device is sensitive to visible and near infrared radiation.



### Notes:

1. All dimensions are in mm.
2. Tolerance is  $\pm 0.25$ mm unless otherwise noted.

## Description

| Part No.       | Chip     | Lens Color  |
|----------------|----------|-------------|
|                | Material |             |
| UT1893-45-0125 | Silicon  | Water clear |


**Absolute Maximum Ratings at Ta=25**

| Parameter                              | Symbol           | Rating                                                                | Unit |
|----------------------------------------|------------------|-----------------------------------------------------------------------|------|
| Power Dissipation                      | P <sub>D</sub>   | 75                                                                    | mW   |
| Collector-emitter voltage              | V <sub>CEO</sub> | 30                                                                    | V    |
| Emitter-collector voltage              | V <sub>ECO</sub> | 5                                                                     | V    |
| Operating Temperature Range            | T <sub>opr</sub> | -25 to +85                                                            |      |
| Storage Temperature Range              | T <sub>stg</sub> | -40 to +100                                                           |      |
| Soldering Temperature(1.6mm from body) | T <sub>sol</sub> | Dip Soldering : 260°C for 5 sec.<br>Hand Soldering : 350°C for 3 sec. |      |


**Electrical and Optical Characteristics:**

| Parameter                            | Symbol               | Condition                                                          | Min. | Typ. | Max. | Unit |
|--------------------------------------|----------------------|--------------------------------------------------------------------|------|------|------|------|
| Collector-emitter breakdown voltage  | V <sub>(BR)CEO</sub> | Ee=0mW/cm <sup>2</sup><br>I <sub>c</sub> =100μA                    | 30   |      |      | V    |
| Emitter-collector breakdown voltage  | V <sub>(BR)ECO</sub> | Ee=0mW/cm <sup>2</sup><br>I <sub>E</sub> =100μA                    | 5    |      |      | V    |
| Collector-emitter saturation voltage | V <sub>(SAT)CE</sub> | Ee=1mW/cm <sup>2</sup><br>I <sub>c</sub> =2mA                      |      |      | 0.3  | V    |
| Rise time                            | T <sub>r</sub>       | V <sub>CE</sub> =5V<br>I <sub>c</sub> =1mA<br>R <sub>L</sub> =1000 |      | 15   |      | μS   |
| Fall time                            | T <sub>f</sub>       |                                                                    |      | 15   |      | μS   |
| Collector Dark Current               | I <sub>CEO</sub>     | Ee=0mW/cm <sup>2</sup><br>V <sub>CE</sub> =20V                     |      |      | 100  | nA   |
| On State Collector Current           | I <sub>c(ON)</sub>   | Ee=1mW/cm <sup>2</sup><br>V <sub>CE</sub> =5V                      | 0.6  | 2.0  |      | mA   |
| Peak Sensitivity Wavelength          | λ <sub>p</sub>       |                                                                    |      | 860  |      | nm   |


## Typical Electrical / Optical Characteristics Curves :




**Fig. 1 Spectral Sensitivity VS. Peak Wavelength**



**Fig. 2 Collector Dark Current VS. Ambient Temperature**



**Fig. 3 Photo Current VS. Irradiance**



**Fig. 4 Collector Current VS. Ambient Temperature**

## Precautions:

### TAKE NOTE OF THE FOLLOWING IN USE OF LED

#### 1. Temperature in use

Since the light generated inside the LED needs to be emitted to outside efficiently, a resin with high light transparency is used; therefore, additives to improve the heat resistance or moisture resistance (silica gel, etc) which are used for semiconductor products such as transistors cannot be added to the resin.

Consequently, the heat resistant ability of the resin used for LED is usually low; therefore, please be careful on the following during use.

Avoid applying external force, stress, and excessive vibration to the resins and terminals at high temperature. The glass transition temperature of epoxy resin used for the LED is approximately 120-130 .

At a temperature exceeding this limit, the coefficient of linear expansion of the resin doubles or more compared to that at normal temperature and the resin is softened.

If external force or stress is applied at that time, it may cause a wire rupture.

#### 2. Soldering

Please be careful on the following at soldering.

After soldering, avoid applying external force, stress, and excessive vibration until the products go to cooling process (normal temperature), <Same for products with terminal leads>

##### (1) Soldering measurements:

Distance between melted solder side to bottom of resin shall be 1.6mm or longer.

##### (2) Dip soldering :

Pre-heat: 90 max. (Backside of PCB), Within 60 seconds.

Solder bath: 260±5 (Solder temperature), Within 5 seconds.

##### (3) Hand soldering: 350 max. (Temperature of soldering iron tip), Within 3 seconds.

#### 3. Insertion

Pitch of the LED leads and pitch of mounting holes need to be same.

#### 4. Others

Since the heat resistant ability of the LED resin is low, SMD components are used on the same PCB, please mount the LED after adhesive baking process for SMD components. In case adhesive baking is done after LED lamp insertion due to a production process reason, make sure not to apply external force, stress, and excessive vibration to the LED and follow the conditions below.

Baking temperature: 120 max. Baking time: Within 60 seconds.


If soldering is done sequentially after the adhesive baking, please perform the soldering after cooling down the LED to normal temperature.

## ENCASED TYPE

### PLASTIC PACKAGE

QUANTITY: 1000 PCS

LEDTECH ELECTRONICS CORP.  
PART NO :LTXXXX-XX  
Q'TY : PCS  
LOT NO :XXXXXXXXXX  
DATE :  
BIN CODE:




### INNER BOX

QUANTITY: 10 PACKETS

TOTAL: 10,000 PCS

|          |              |      |      |      |       |
|----------|--------------|------|------|------|-------|
| PART NO. | LXXXXX-XX-XX |      |      |      |       |
| LOT NO.  | XXXXXXXXXX   |      |      |      |       |
| BIN CODE | Xx X         | Xx X | Xx X | Xx X | TOTAL |
| QUANTITY | PCS          | PCS  | PCS  | PCS  | PCS   |
| DATE     | XXXX, XX, XX |      |      |      |       |



### OUTER CARTON

QUANTITY: 4 BOX

TOTAL: 40,000 PCS

|                 |              |
|-----------------|--------------|
| C/T NO.<br>箱 號  | XX           |
| PART NO.<br>料 號 | LXXXXX-XX-XX |
| QUANTITY<br>數 量 | PCS          |
| N.W.<br>淨 重     | KGS          |
| G.W.<br>毛 重     | KGS          |
| REMARK<br>備 註   |              |

