

SI-8400L/8500L Series

Separate Excitation Switching Mode Regulator ICs with Coil

Features

- Switching ICs/Coil combined type
- Requires only 2 discrete components
- Low switching noise
- No heatsink required
- Built-in overcurrent and thermal protection circuits
- Built-in soft start circuit (Output ON/OFF available)...SI-8500L Series

Applications

- Telephone power supplies
- Onboard local power supplies

Lineup

Part Number	SI-8401L	SI-8501L
V _o (V)	5.0	5.0
I _o (A)	0.5	1.0

Absolute Maximum Ratings

Parameter	Symbol	Ratings		Unit
		SI-8400L	SI-8500L	
DC Input Voltage	V _{IN}	35		V
Power Dissipation	P _D	1.25	3	W
Junction Temperature	T _j	+100		°C
Storage Temperature	T _{stg}	−25 to +85		°C

Recommended Operating Conditions

Parameter	Symbol	Ratings	Unit
		SI-8401L	
DC Input Voltage Range	V _{IN}	7 to 33	V
Output Current Range	I _o	0 to 0.5	A
Operating Temperature Range	T _{op}	−20 to +85	°C

Parameter	Symbol	Ratings	Unit
		SI-8501L	
DC Input Voltage Range	V _{IN}	7 to 33	V
Output Current Range	I _o	0 to 1.0	A
Operating Temperature Range	T _{op}	−20 to +85	°C

Electrical Characteristics

(T_a=25°C)


Parameter	Symbol	Ratings			Unit
		SI-8401L			
		min.	typ.	max.	
Output Voltage	V _O	4.80	5.00	5.20	V
	Conditions	V _{IN} =20V, I _O =0.3A			
Efficiency	η		80		%
	Conditions	V _{IN} =20V, I _O =0.3A			
Oscillation Frequency	f		60		kHz
	Conditions	V _{IN} =20V, I _O =0.3A			
Line Regulation	ΔV _{OLINE}		80	100	mV
	Conditions	V _{IN} =10 to 30V, I _O =0.3A			
Load Regulation	ΔV _{OLOAD}		30	40	mV
	Conditions	V _{IN} =20V, I _O =0.1 to 0.4A			
Temperature Coefficient of Output Voltage	ΔV _O /ΔT _a		±0.5		mV/°C
Switching Ripple Voltage (C ₂ =470μF)	ΔV _r		20	40	mV _{P-P}
	Conditions	V _{IN} =20V, I _O =0.3A			
Overcurrent Protection Starting Current	I _{SL}	0.55			A
	Conditions	V _{IN} =10V			

(T_a=25°C)


Parameter	Symbol	Ratings			Unit
		SI-8501L			
		min.	typ.	max.	
Output Voltage	V _O	4.80	5.00	5.20	V
	Conditions	V _{IN} =20V, I _O =0.5A			
Efficiency	η		83		%
	Conditions	V _{IN} =20V, I _O =0.5A			
Oscillation Frequency	f		60		kHz
	Conditions	V _{IN} =20V, I _O =0.5A			
Line Regulation	ΔV _{OLINE}		70	130	mV
	Conditions	V _N =10 to 30V, I _O =0.5A			
Load Regulation	ΔV _{OLOAD}		30	55	mV
	Conditions	V _N =20V, I _O =0.2 to 0.8A			
Temperature Coefficient of Output Voltage	ΔV _O /ΔT _a		±0.5		mV/°C
Switching Ripple Voltage (C ₂ =470μF)	ΔV _r		45		mV _{P-P}
	Conditions	V _{IN} =20V, I _O =0.5A			
Overcurrent Protection Starting Current	I _{S1}	1.1			A
	Conditions	V _{IN} =18V			

External Dimensions (Non-package type [EI-12.5 core/EI-19 core])


(Unit : mm)



Block Diagram



Typical Connection Diagram



Ta-Pd Characteristics

