

High frequency ground wire choke, shrink hose



#### Description

- Ground wire chokes (earth line chokes)
- Wire leads

#### Standards

- EN 60938

#### Applications

- Separating the main earth line to periphery devices
- This type of chokes permits the building of a system free of ground wire loops

#### Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#),  
[Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#),  
[SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)



#### Technical Data

Rated Current	16 - 25 A @ Ta 40 °C
Rated inductance	0.02 - 0.04 mH, Tol. ±15%
Power Operating Frequency	> 5 MHz
Terminal technic	Wire leads
Weight	17 - 51 g
Material: Housing	UL 94V-0
Sealing Compound	UL 94V-0


Isolation Voltage	2 kV eff., winding to ambient
Climatic Category	25/100/21 acc. to IEC 60068-1
Allowable Operation Temp.	-25 °C to 100 °C

#### Dimension

16A 25A



## Diagrams



Example of a perfect earth line system using a radiator and an earth line choke

## Variants

I <sub>n</sub> [A]	L <sub>n</sub> [mH]	R <sub>cu</sub> [mΩ]	f <sub>RES</sub> [MHz]	Weight [g]	Packing unit [pcs.]	Order Number
16	0.02	15	30	17g	100	DEHL-10-0001
25	0.04	10	20	51g	50	DEH-15-0001

■ Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>