




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DDC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2070	A	Released	JN	09-03-09	JWM	09-03-09	JWM	09-03-09



Specification

1. Rated Voltage: 110VAC
2. Operating Voltage: 100~130VAC
3. Max. Rated Current: 20mA at 110VAC
4. Min. Sound Pressure Level: 95 dB at 110VAC/10cm
5. Resonant Frequency: 2.9 ± 0.5 KHz
6. Tone Nature: Continuous
7. Case Material: PBT/Black
8. Operating Temperature: $-20 \sim +80^{\circ}\text{C}$
9. Store Temperature: $-30 \sim +100^{\circ}\text{C}$
10. Weight: 40g

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Jason Nash

DATE:

09-03-09

CHECKED BY:

Jason Nash

DATE:

09-03-09

APPROVED BY:

Jason Nash

DATE:

09-03-09

DRAWING TITLE:

Piezo Buzzer

SIZE

A

DWG. NO.

MCKPI-G4320-110VAC-3675

ELECTRONIC FILE

25R0690.dwg

REV

A

SCALE:

NTS

U.O.M.:

INCHES [mm]

SHEET:

1 OF 1