



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



PRODUCT NO. 51939-315... NOTE 3	ROWS DCBA	POWER		SIGNAL				POWER		E2	
		E1	P1	P2	1	2	3	4	P3		P4



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL
PA	[N/A]	POWER
X	OMITTED	OMITTED

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER	
ltr	ecn no.	dr	date	linear	0.X ± 0.3	angles	0° ± 2°	COPY	
A	DG07-0334	SH	08/17/07		0.XX ± 0.13			projection	
					0.XXX ± 0.051			title	
								2P+16S+2P	
								RIGHT ANGLE SOLDER HEADER	
								product family	
								PwrBlade	
								code	
								213	
								size	
								dwg no	
								51939-315	
								sheet	
								1 of 4	

CONFIDENTIAL			
www.fciconnect.com			
MIM			
scale 1:1			
cage code 22526			

sheet index	revision sheet	A	A	A	A	A	A
		1	2	3	4		

Pro/E


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.


All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.




PRODUCT NUMBER
51939-315-
NOTE: 3




BROKEN-OUT SECTION A-A
SCALE 2:1



BROKEN-OUT SECTION B-B
SCALE 2:1



SECTION C-C



PARTIAL SECTION E-E

CONFIDENTIAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection		COPY		www.fciconnect.com	
A				angles	0.XX ±0.13	MIM		title		2P+16S+2P	
				dr	0.XXX ±0.051	1:1		product family		PwrBlade	
				enr	0° ±2°	scale		size		code	
				chr	Sincere He 08/17/07	A		dwg no		213	
				appd	Sincere He 08/17/07	A		51939-315		sheet	
					Gary Hsieh 08/17/07					2 of 4	
					Joseph Hsia 08/17/07						
sheet index	revision sheet										

cage code 22526


Pro/E

Tous droits strictement réservés. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-315-
NOTE: 3



RECOMMENDED PCB LAYOUT

CONFIDENTIAL

mat'l code				SEE NOTE	tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ± 0.3	COPY		www.fciconnect.com		
A					0.XX ± 0.13	projection		title		
				angles	0.XXX ± 0.051			2P+16S+2P RIGHT ANGLE SOLDER HEADER		
				dr	Sincere He 08/17/07	MIM		product family		code
				enr	Sincere He 08/17/07			PwrBlade		213
				chr	Gary Hsieh 08/17/07	scale		size		sheet
				appd	Joseph Hsia 08/17/07	1:1		dwg no		3 of 4
sheet index		revision sheet						A		51939-315

cage code 22526

Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-315--
NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- 2. HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
- 3. 51939-315; 51939-315LF PLATING SPEC. SEE PRINT:10064183
- 4. MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
- 5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
- 6. PACKAGED IN TRAYS.

PCB NOTES:

- 7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
- 9. $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER 0.03
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
- 10. "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- 11. CONNECTOR KEEP-OUT ZONE.

CONFIDENTIAL

mat'l code				SEE NOTE	tolerances unless otherwise specified	CUSTOMER	FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ± 0.3	COPY	title	
A					0.XX ± 0.13	projection	2P+16S+2P RIGHT ANGLE SOLDER HEADER	
				angles	0.XXX ± 0.051		product family PwrBlade code	
				dr	0° ± 2°	MIM	size	213
				enr	Sincere He 08/17/07	← MIM →	dwg no	sheet
				chr	Sincere He 08/17/07	scale	51939-315	4 of 4
				appd	Gary Hsieh 08/17/07	1:1		
					Joseph Hsia 08/17/07			
sheet index	revision sheet							

cage code 22526

Pro/E